

Zero Aperture, 37mm Max. Aperture, Iris Diaphragm



Stock #53-908 3-4 DAYS

⊖ 1 ⊕ **€80,00**

ADD TO CART

Qty 1-9
€80,00
Qty 10+
€70,60
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
0.00

Maximum Aperture (mm):

37.0
Outer Diameter (mm): 54.0
Construction: Black Anodized Aluminum, Black Spring Steel Leaves, Stainless Steel Pins
Lever Diameter (mm): 3.00
Lever Length (mm): 12.60
Number of Leaves: Two Sets of 8
Spacing of Leaf Layers (mm): 3.1
Thickness (mm): 7.50

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)