

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Flat Mirrors](#) / [Precision Polished Metal Coatings](#)
TECHSPEC® ZERODUR® $\lambda/10$ First Surface Mirrors See More by [SCHOTT Optical Components](#)


- Precision ZERODUR® Substrates
- $\lambda/10$ Flatness
- Low Coefficient of Thermal Expansion

Common Specifications

Physical & Mechanical Properties

Back Surface:	Commercial Polish	Bevel:	Protective as needed
Clear Aperture (%):	90	Edges:	Ground
Parallelism (arcsec):	30		

Optical Properties

Surface Flatness (P-V):	$\lambda/10$		
Substrate:	ZERODUR®	Surface Quality:	20-10
Coating Type:	Metal		

Material Properties

Coefficient of Thermal Expansion CTE ($10^{-6}/^{\circ}\text{C}$):	0.1
--	-----

Technical Information

Products

Dia. (mm)	Surface Flatness (P-V)	Dimensions (mm)	Coating Specification	Coating	Thickness (mm)	Stock Number	Price	Buy
5.00	λ/10	-	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	2.00	#17-718	€99,50 Volume Pricing	3 In Stock
5.00	λ/10	-	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	2.00	#17-719	€99,50 Volume Pricing	3 In Stock
5.00	λ/10	-	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	2.00	#17-720	€127,00 Volume Pricing	4 In Stock
5.00	λ/10	-	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	2.00	#17-721	€118,00 Volume Pricing	1 In Stock
-	λ/10	5.0 x 5.0	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	2.00	#17-722	€99,50 Volume Pricing	2 In Stock
#17-723 New								
 New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!								
-	λ/10	5.0 x 5.0	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	2.00		€99,50 Volume Pricing	2 In Stock
-	λ/10	5.0 x 5.0	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	2.00	#17-724	€127,00 Volume Pricing	1 In Stock

-	$\lambda/10$	5.0 x 5.0	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#17-725	€118,00 Volume Pricing	Contact Us
10.00	$\lambda/10$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#39-846	€99,50 Volume Pricing	9 In Stock
10.00	$\lambda/10$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#24-265	€99,50 Volume Pricing	2 In Stock
10.00	$\lambda/10$	-	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#39-874	€118,00 Volume Pricing	Contact Us
10.00	$\lambda/10$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#39-860	€127,00 Volume Pricing	1 In Stock
-	$\lambda/10$	10.0 x 10.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#39-847	€99,50 Volume Pricing	Contact Us
-	$\lambda/10$	10.0 x 10.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#24-266	€99,50 Volume Pricing	1 In Stock
-	$\lambda/10$	10.0 x 10.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#39-875	€118,00 Volume Pricing	20+ In Stock
-	$\lambda/10$	10.0 x 10.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#39-861	€127,00 Volume Pricing	2 In Stock
12.50	$\lambda/10$	-	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	3.00	#17-735	€122,00 Volume Pricing	3 In Stock
12.50	$\lambda/10$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	3.00	#17-734	€135,00 Volume Pricing	1 In Stock
12.50	$\lambda/10$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	3.00	#17-732	€102,00 Volume Pricing	4 In Stock

12.50	$\lambda/10$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	3.00	#17-733	€102,00 Volume Pricing	2 In Stock
-	$\lambda/10$	12.5 x 12.5	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	3.00	#17-736	€102,00 Volume Pricing	2 In Stock
-	$\lambda/10$	12.5 x 12.5	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	3.00	#17-737	€102,00 Volume Pricing	5 In Stock
-	$\lambda/10$	12.5 x 12.5	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	3.00	#17-739	€122,00 Volume Pricing	3 In Stock
-	$\lambda/10$	12.5 x 12.5	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	3.00	#17-738	€135,00 Volume Pricing	3 In Stock
15.00	$\lambda/10$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	3.00	#39-848	€106,00 Volume Pricing	4 In Stock
15.00	$\lambda/10$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	3.00	#24-267	€106,00 Volume Pricing	3 In Stock
15.00	$\lambda/10$	-	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	3.00	#39-876	€127,00 Volume Pricing	5 In Stock
15.00	$\lambda/10$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	3.00	#39-862	€139,00 Volume Pricing	7 In Stock
-	$\lambda/10$	15.0 x 15.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	3.00	#39-849	€106,00 Volume Pricing	3 In Stock
-	$\lambda/10$	15.0 x 15.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	3.00	#24-268	€106,00 Volume Pricing	2 In Stock
-	$\lambda/10$	15.0 x 15.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	3.00	#39-877	€127,00 Volume Pricing	Contact Us

-	$\lambda/10$	15.0 x 15.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	3.00	#39-863	€142,00 Volume Pricing	1 In Stock
20.00	$\lambda/10$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	3.00	#39-850	€118,00 Volume Pricing	Contact Us
20.00	$\lambda/10$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	3.00	#24-269	€118,00 Volume Pricing	3 In Stock
20.00	$\lambda/10$	-	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	3.00	#39-883	€142,00 Volume Pricing	Contact Us
20.00	$\lambda/10$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	3.00	#39-864	€158,00 Volume Pricing	20+ In Stock
-	$\lambda/10$	20.0 x 20.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	3.00	#39-851	€118,00 Volume Pricing	5 In Stock
-	$\lambda/10$	20.0 x 20.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	3.00	#24-270	€118,00 Volume Pricing	1 In Stock
-	$\lambda/10$	20.0 x 20.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	3.00	#39-909	€142,00 Volume Pricing	Contact Us
-	$\lambda/10$	20.0 x 20.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	3.00	#39-865	€155,00 Volume Pricing	2 In Stock
25.00	$\lambda/10$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	4.00	#39-852	€129,00 Volume Pricing	2 In Stock
25.00	$\lambda/10$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	4.00	#24-271	€127,00 Volume Pricing	Contact Us
25.00	$\lambda/10$	-	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	4.00	#39-910	€150,00 Volume Pricing	Contact Us

25.00	$\lambda/10$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	4.00	#39-866	€167,00 Volume Pricing	Contact Us
-	$\lambda/10$	25.0 x 25.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	4.00	#39-853	€127,00 Volume Pricing	1 In Stock
-	$\lambda/10$	25.0 x 25.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	4.00	#24-272	€127,00 Volume Pricing	2 In Stock
-	$\lambda/10$	25.0 x 25.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	4.00	#39-911	€150,00 Volume Pricing	5 In Stock
-	$\lambda/10$	25.0 x 25.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	4.00	#39-867	€164,00 Volume Pricing	1 In Stock
-	$\lambda/10$	25.0 x 35.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	5.00	#29-303	€193,00 Volume Pricing	1 In Stock
-	$\lambda/10$	25.0 x 35.0	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	5.00	#29-304	€169,00 Volume Pricing	4 In Stock
-	$\lambda/10$	25.0 x 35.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	5.00	#29-305	€146,00 Volume Pricing	9 In Stock
-	$\lambda/10$	25.0 x 35.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	5.00	#29-306	€146,00 Volume Pricing	8 In Stock
25.40	$\lambda/10$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	6.35	#17-754	€146,00 Volume Pricing	Contact Us
25.40	$\lambda/10$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	6.35	#17-755	€146,00 Volume Pricing	Contact Us
25.40	$\lambda/10$	-	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	6.35	#17-757	€164,00 Volume Pricing	Contact Us

25.40	$\lambda/10$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	6.35	#17-756	€181,00 Volume Pricing	Contact Us
30.00	$\lambda/10$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	5.00	#17-758	€176,00 Volume Pricing	4 In Stock
30.00	$\lambda/10$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	5.00	#17-759	€176,00 Volume Pricing	5 In Stock
30.00	$\lambda/10$	-	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	5.00	#17-761	€193,00 Volume Pricing	Contact Us
30.00	$\lambda/10$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	5.00	#17-760	€216,00 Volume Pricing	2 In Stock
-	$\lambda/10$	30.0 x 30.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	5.00	#17-762	€176,00 Volume Pricing	5 In Stock
-	$\lambda/10$	30.0 x 30.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	5.00	#17-763	€176,00 Volume Pricing	4 In Stock
-	$\lambda/10$	30.0 x 30.0	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	5.00	#17-765	€193,00 Volume Pricing	1 In Stock
-	$\lambda/10$	30.0 x 30.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	5.00	#17-764	€216,00 Volume Pricing	1 In Stock
40.00	$\lambda/10$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	5.00	#17-779	€199,00 Volume Pricing	Contact Us
40.00	$\lambda/10$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	5.00	#17-780	€199,00 Volume Pricing	9 In Stock
40.00	$\lambda/10$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	5.00	#17-781	€263,00 Volume Pricing	2 In Stock

40.00	$\lambda/10$	-	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	5.00	#17-782	€238,00 Volume Pricing	1 In Stock
-	$\lambda/10$	40.0 x 40.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	5.00	#17-783	€199,00 Volume Pricing	2 In Stock
-	$\lambda/10$	40.0 x 40.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	5.00	#17-784	€199,00 Volume Pricing	2 In Stock
-	$\lambda/10$	40.0 x 40.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	5.00	#17-785	€263,00 Volume Pricing	1 In Stock
-	$\lambda/10$	40.0 x 40.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	5.00	#17-786	€238,00 Volume Pricing	1 In Stock
50.00	$\lambda/10$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	5.00	#39-854	€217,00 Volume Pricing	10 In Stock
50.00	$\lambda/10$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	5.00	#24-273	€217,00 Volume Pricing	2 In Stock
50.00	$\lambda/10$	-	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	5.00	#39-916	€259,00 Volume Pricing	Contact Us
50.00	$\lambda/10$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	5.00	#39-868	€280,00 Volume Pricing	2 In Stock
-	$\lambda/10$	50.0 x 50.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	5.00	#39-855	€217,00 Volume Pricing	5 In Stock
-	$\lambda/10$	50.0 x 50.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	5.00	#24-274	€217,00 Volume Pricing	5 In Stock
-	$\lambda/10$	50.0 x 50.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	5.00	#39-917	€259,00 Volume Pricing	4 In Stock

-	$\lambda/10$	50.0 x 50.0	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	5.00	#39-870	€280,00 Volume Pricing	7 In Stock
75.00	$\lambda/10$	-	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	7.50	#17-793	€530,00 Volume Pricing	Contact Us
75.00	$\lambda/10$	-	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	7.50	#17-794	€530,00 Volume Pricing	5 In Stock
75.00	$\lambda/10$	-	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	7.50	#17-795	€660,00 Volume Pricing	Contact Us
75.00	$\lambda/10$	-	$R_{avg} > 98\% @$ 450 - 800nm $R_{avg} > 98.5\%$ $@ 2000 -$ 10,000nm	Protected Silver (450- 10000nm)	7.50	#17-796	€605,00 Volume Pricing	Contact Us
-	$\lambda/10$	75.0 x 75.0	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	7.50	#17-797	€530,00 Volume Pricing	1 In Stock
-	$\lambda/10$	75.0 x 75.0	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	7.50	#17-798	€530,00 Volume Pricing	1 In Stock
-	$\lambda/10$	75.0 x 75.0	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	7.50	#17-799	€660,00 Volume Pricing	4 In Stock
-	$\lambda/10$	75.0 x 75.0	$R_{avg} > 98\% @$ 450 - 800nm $R_{avg} > 98.5\%$ $@ 2000 -$ 10,000nm	Protected Silver (450- 10000nm)	7.50	#17-800	€605,00 Volume Pricing	Contact Us
100.00	$\lambda/10$	-	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	10.00	#17-801	€635,00 Volume Pricing	Contact Us
100.00	$\lambda/10$	-	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	10.00	#17-802	€635,00 Volume Pricing	1 In Stock
100.00	$\lambda/10$	-	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	10.00	#17-803	€920,00 Volume Pricing	1 In Stock

100.00	$\lambda/10$	-	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	10.00	#17-804	€840,00 Volume Pricing	Contact Us
-	$\lambda/10$	100.0 x 100.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	10.00	#17-805	€635,00 Volume Pricing	2 In Stock
-	$\lambda/10$	100.0 x 100.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	10.00	#17-806	€635,00 Volume Pricing	3 In Stock
-	$\lambda/10$	100.0 x 100.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	10.00	#17-807	€920,00 Volume Pricing	2 In Stock
-	$\lambda/10$	100.0 x 100.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	10.00	#17-808	€840,00 Volume Pricing	1 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com