


[All Products](#) /
 [Optics](#) /
 [Optical Filters](#) /
 [Color and Absorptive Filters](#)

Additive and Subtractive Dichroic Color Filters



- High Saturation Dichroic Type
- Matrix of Sizes and Sets
- Precision Glass Substrate

Common Specifications

Physical & Mechanical Properties

Thickness (mm):	2.00 Nominal	Dimensional Tolerance (mm):	±0.25
Clear Aperture (%):	≥85		

Optical Properties


Angle of Incidence (°):	0		
Substrate:	BOROFLOAT®	Surface Quality:	80-50

Environmental & Durability Factors


Operating Temperature (°C):	<100
-----------------------------	------

Technical Information

Additive Filters Typical Transmittance Curves



Subtractive Filters Typical Transmittance Curves



Products

Dia. (mm)	Dimensions (mm)	Color	Stock Number	Price	Buy
12.50	-	Blue	#52-530	€23,69 Volume Pricing	20+ In Stock
-	12.5 x 12.5	Blue	#11-482	€23,69 Volume Pricing	5 In Stock
25.00	-	Blue	#52-531	€27,30 Volume Pricing	20+ In Stock
-	25.0 x 25.0	Blue	#11-479	€27,30 Volume Pricing	16 In Stock
50.00	-	Blue	#52-532	€42,23 Volume Pricing	2 In Stock
-	50.0 x 50.0	Blue	#30-635	€41,97 Volume Pricing	Contact Us
12.50	-	Cyan	#52-536	€23,69 Volume Pricing	5 In Stock
25.00	-	Cyan	#52-537	€27,30 Volume Pricing	20+ In Stock
50.00	-	Cyan	#52-538	€42,23 Volume Pricing	20+ In Stock
-	50.0 x 50.0	Cyan	#39-912	€42,23 Volume Pricing	7 In Stock
12.50	-	Green	#52-533	€23,69 Volume Pricing	20+ In Stock
-	12.5 x 12.5	Green	#11-483	€23,69 Volume Pricing	6 In Stock
25.00	-	Green	#52-534	€27,30 Volume Pricing	20+ In Stock
-	25.0 x 25.0	Green	#11-480	€27,30 Volume Pricing	8 In Stock
50.00	-	Green	#52-535	€42,23 Volume Pricing	10 In Stock
-	50.0 x 50.0	Green	#46-139	€42,23 Volume Pricing	14 In Stock
12.50	-	Magenta	#52-539	€23,69 Volume Pricing	5 In Stock

25.00	-	Magenta	#52-540	€27,30 Volume Pricing	20+ In Stock
50.00	-	Magenta	#52-541	€42,23 Volume Pricing	20+ In Stock
-	50.0 x 50.0	Magenta	#39-913	€42,23 Volume Pricing	14 In Stock
12.50	-	Red	#52-527	€23,69 Volume Pricing	20+ In Stock
-	12.5 x 12.5	Red	#11-484	€23,69 Volume Pricing	20+ In Stock
25.00	-	Red	#52-528	€27,30 Volume Pricing	3 In Stock
-	25.0 x 25.0	Red	#11-481	€27,30 Volume Pricing	20+ In Stock
50.00	-	Red	#52-529	€42,23 Volume Pricing	Contact Us
-	50.0 x 50.0	Red	#30-634	€41,97 Volume Pricing	20+ In Stock
12.50	-	Yellow	#52-542	€23,69 Volume Pricing	20+ In Stock
25.00	-	Yellow	#52-543	€27,30 Volume Pricing	20+ In Stock
50.00	-	Yellow	#52-544	€42,23 Volume Pricing	9 In Stock
-	50.0 x 50.0	Yellow	#30-637	€41,97 Volume Pricing	20+ In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com