


[All Products](#) / [Test Targets](#) / [Distortion Test Targets](#)

Fixed Frequency Grid Distortion Targets



- For Distortion Measurement and Calibration of Imaging Systems
- Chrome on Soda Lime Glass or Chrome on White Ivory Glass Versions
- NIST Certificate of Accuracy Included

Common Specifications

General

NIST Certification:

Serialized NIST Traceable Certificate Included

Physical & Mechanical Properties

Dot Diameter Tolerance
(mm): ± 0.002

Dot Spacing Tolerance
(mm): ± 0.002 Center to Center

Flatness (inches): 0.001

Optical Properties



Coating: Reflective First Surface
Chromium
 $R_{\text{abs}} = 50\% \pm 5\%$ @
550nm

Optical Density OD
(Average): >3.0

Surface Quality: 40-20

Technical Information

Products

Title	Stock Number	Price	Buy
25 x 25mm, 0.125mm Spacing, Glass Distortion Target	#58-509	€751,90 Volume Pricing	10 In Stock
#58-527 Clearance			
			
25 x 25mm, 0.25mm Spacing, Glass Distortion Target	Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	€669,50 Volume Pricing	2 In Stock
#57-981 Clearance			
			
25 x 25mm, 0.5mm Spacing, Glass Distortion Target	Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	€612,85 Volume Pricing	Contact Us
25 x 25mm, 0.125mm Spacing, White Ivory Distortion Target	#59-209	€885,80 Volume Pricing	20+ In Stock

[#59-210 Clearance](#)



25 x 25mm,
0.50mm Spacing,
White Ivory
Distortion Target

Clearance

Availability is limited, so buy
before these products disappear.
Sorry, we cannot accept returns.
Receive up to 80% off select
products.

€731,30
[Volume Pricing](#)

8 In Stock

[#63-983 Clearance](#)



25 x 25mm,
0.250mm Spacing,
White Ivory
Distortion Target

Clearance

Availability is limited, so buy
before these products disappear.
Sorry, we cannot accept returns.
Receive up to 80% off select
products.

€787,95
[Volume Pricing](#)

5 In Stock

[#63-984 Clearance](#)



25 x 25mm,
1.000mm Spacing,
White Ivory
Distortion Target

Clearance

Availability is limited, so buy
before these products disappear.
Sorry, we cannot accept returns.
Receive up to 80% off select
products.

€684,95
[Volume Pricing](#)

5 In Stock

[#58-536 Clearance](#)



50 x 50mm,
0.5mm Spacing,
Glass Distortion
Target

Clearance

Availability is limited, so buy
before these products disappear.
Sorry, we cannot accept returns.
Receive up to 80% off select
products.

€726,15
[Volume Pricing](#)

3 In Stock

50 x 50mm,
1.0mm Spacing,
Glass Distortion
Target

[#57-983](#)

€623,15
[Volume Pricing](#)

17 In Stock

50 x 50mm,
1.0mm Spacing,
White Ivory
Distortion Target

[#59-211](#)

€885,80
[Volume Pricing](#)

4 In Stock

50 x 50mm,
0.25mm Spacing,
Glass Distortion
Target

[#59-213](#)

€787,95
[Volume Pricing](#)

5 In Stock

50 x 50mm,
1.0mm Spacing,
Glass Distortion
Target

[#62-211](#)

€710,70
[Volume Pricing](#)

1 In Stock

[#63-986 Clearance](#)



50 x 50mm,
0.500mm Spacing,
White Ivory
Distortion Target

Clearance

Availability is limited, so buy
before these products disappear.
Sorry, we cannot accept returns.
Receive up to 80% off select
products.

€937,30
[Volume Pricing](#)

3 In Stock

100 x 100mm,
2.0mm Spacing,
Glass Distortion
Target

[#57-985](#)

€1.333,85
[Volume Pricing](#)

6 In Stock

100 x 100mm, 0.5mm Spacing, Glass Distortion Target	#59-215	€1.405,95 Volume Pricing	3 In Stock
100 x 100mm, 1.0mm Spacing, Glass Distortion Target	#59-217	€1.369,90 Volume Pricing	Contact Us
100 x 100mm, 1.0mm Spacing, Glass Distortion Target	#62-213	€1.390,50 Volume Pricing	3 In Stock
100 x 100mm, 0.500mm Spacing, White Ivory Distortion Target	#63-988	€1.879,75 Volume Pricing	1 In Stock
100 x 100mm, 1.000mm Spacing, White Ivory Distortion Target	#63-990	€1.802,50 Volume Pricing	3 In Stock
100 x 100mm, 2.0mm Spacing, White Ivory Distortion Target	#59-212	€1.709,80 Volume Pricing	1 In Stock
150 x 150mm, 2mm Spacing, Glass Distortion Target	#58-507	€2.157,85 Volume Pricing	6 In Stock
150 x 150mm, 1.0mm Spacing, Glass Distortion Target	#62-207	€2.157,85 Volume Pricing	4 In Stock
150 x 150mm, 1.000mm Spacing, White Ivory Distortion Target	#63-991	€3.053,95 Volume Pricing	3 In Stock
150 x 150mm, 2.000mm Spacing, White Ivory Distortion Target	#63-992	€3.053,95 Volume Pricing	2 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com