




[All Products](#) / [Optomechanics](#) / [Iris and Apertures](#) / [Iris Diaphragms](#)

## **TECHSPEC®** High Performance Motorizable Irises



- Fast Accurate Repeatable Motion
- Dual Control Gear and Lever Mechanics
- Removable Pin for OEM Integration
- Anti-Reflection (AR) Leaves Available
- Iris Diaphragm Mounts and Motor Sold Separately

Technical Information



## Products

| Minimum Aperture (mm) | Maximum Aperture (mm) | Outer Diameter (mm) | Number of Leaves | Construction                                       | Stock Number            | Price                                     | Buy          |
|-----------------------|-----------------------|---------------------|------------------|----------------------------------------------------|-------------------------|-------------------------------------------|--------------|
| 0.9                   | 7.0                   | 12.0                | 8                | Brass-Spring Steel                                 | <a href="#">#34-286</a> | €122,57<br><a href="#">Volume Pricing</a> | 2 In Stock   |
| 0.9                   | 8.0                   | 14.8                | 8                | Brass-Spring Steel                                 | <a href="#">#34-287</a> | €75,19<br><a href="#">Volume Pricing</a>  | 20+ In Stock |
| 1.0                   | 12.0                  | 19.8                | 10               | Brass-Spring Steel                                 | <a href="#">#34-288</a> | €81,37<br><a href="#">Volume Pricing</a>  | 20+ In Stock |
| 1.2                   | 15.0                  | 24.0                | 12               | Brass-Spring Steel                                 | <a href="#">#34-289</a> | €81,37<br><a href="#">Volume Pricing</a>  | 17 In Stock  |
| 1.2                   | 18.0                  | 28.0                | 12               | Brass-Spring Steel                                 | <a href="#">#34-290</a> | €81,37<br><a href="#">Volume Pricing</a>  | 13 In Stock  |
| 1.4                   | 22.0                  | 33.0                | 14               | Brass-Spring Steel                                 | <a href="#">#34-291</a> | €101,97<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 1.4                   | 25.0                  | 37.0                | 14               | Brass-Spring Steel                                 | <a href="#">#34-292</a> | €101,97<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 1.5                   | 28.0                  | 40.0                | 16               | Brass-Spring Steel                                 | <a href="#">#34-293</a> | €107,12<br><a href="#">Volume Pricing</a> | 14 In Stock  |
| 1.5                   | 34.0                  | 49.0                | 14               | Brass-Spring Steel                                 | <a href="#">#34-294</a> | €122,57<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 0.9                   | 7.0                   | 12.0                | 8                | Brass-Spring Steel, Anti-Reflection (AR) Leaves    | <a href="#">#24-202</a> | €172,01<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 1.0                   | 12.0                  | 19.8                | 10               | Brass-Spring Steel, Anti-Reflection (AR) Leaves    | <a href="#">#24-203</a> | €116,39<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 1.4                   | 22.0                  | 33.0                | 14               | Brass-Spring Steel, Anti-Reflection (AR) Leaves    | <a href="#">#24-204</a> | €143,17<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 1.5                   | 28.0                  | 40.0                | 16               | Aluminum-Spring Steel, Anti-Reflection (AR) Leaves | <a href="#">#24-205</a> | €152,44<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 1.5                   | 34.0                  | 49.0                | 14               | Brass-Spring Steel, Anti-Reflection (AR) Leaves    | <a href="#">#24-206</a> | €172,01<br><a href="#">Volume Pricing</a> | 11 In Stock  |





Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

[www.edmundoptics.com](http://www.edmundoptics.com)