

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Flat Mirrors](#) / [Laser Mirrors](#)

TECHSPEC® Uncoated Laser Window Substrates



- Up to 10-5 Surface Quality and $\lambda/10$ Surface Flatness Available
- Fused Silica or N-BK7 Material
- Standard Imperial Sizes for Drop-in Replacement Solutions
- [Laser Line Coated Versions](#) Available
- [Mirror Substrates](#) Also Available

Common Specifications

Physical & Mechanical Properties

Edges: Fine Ground

Optical Properties

Coating: Uncoated

Technical Information

Products

Coating	Substrate	Fused Silica Grade	Dia. (mm)	Thickness (mm)	Stock Number	Price	Buy
Uncoated	Fused Silica	7980 KrF 0A	12.50	3.00	#48-022	€128,75 Volume Pricing	20+ In Stock
Uncoated	Fused Silica	7980	12.70	1.00	#11-749	€100,94 Volume Pricing	Contact Us
Uncoated	Fused Silica	7979 0G	12.70	1.00	#11-752	€109,18 Volume Pricing	20+ In Stock
Uncoated	Fused Silica	7980 0F	12.70	3.18	#37-693	€128,75 Volume Pricing	20+ In Stock
Uncoated	N-BK7	-	12.70	6.35	#38-055	€118,45 Volume Pricing	20+ In Stock
Uncoated	Fused Silica	7980 0F	12.70	6.35	#37-688	€128,75 Volume Pricing	20+ In Stock
Uncoated	N-BK7	-	19.10	6.35	#38-056	€128,75 Volume Pricing	17 In Stock
Uncoated	Fused Silica	7980 0F	19.10	6.35	#38-911	€139,05 Volume Pricing	20+ In Stock
Uncoated	Fused Silica	7980 KrF 0A	25.00	3.00	#48-023	€159,65 Volume Pricing	20+ In Stock
Uncoated	Fused Silica	7980 0G	25.40	1.00	#11-750	€119,48 Volume Pricing	20+ In Stock
Uncoated	Fused Silica	7979 0G	25.40	1.00	#11-753	€127,72 Volume Pricing	10 In Stock
Uncoated	Fused Silica	7980 0F	25.40	3.18	#37-694	€154,50 Volume Pricing	20+ In Stock
Uncoated	N-BK7	-	25.40	6.35	#38-057	€149,35 Volume Pricing	20+ In Stock
Uncoated	Fused Silica	7980 0F	25.40	6.35	#37-689	€154,50 Volume Pricing	20+ In Stock
Uncoated	N-BK7	-	38.10	6.35	#11-450	€195,70 Volume Pricing	20+ In Stock
Uncoated	Fused Silica	7980 0F	38.10	6.35	#38-912	€211,15 Volume Pricing	20+ In Stock

Uncoated	N-BK7	-	38.10	9.53	#38-058	€195,70 Volume Pricing	20+ In Stock
Uncoated	Fused Quartz	-	50.00	2.00	#37-666	€61,80 Volume Pricing	20+ In Stock
Uncoated	Fused Silica	7979 0G	50.80	1.00	#11-751	€208,06 Volume Pricing	20+ In Stock
Uncoated	Fused Silica	7979 0G	50.80	1.00	#11-754	€229,69 Volume Pricing	20+ In Stock
Uncoated	Fused Silica	7980 0F	50.80	6.35	#37-690	€257,50 Volume Pricing	20+ In Stock
Uncoated	N-BK7	-	50.80	9.53	#38-059	€247,20 Volume Pricing	15 In Stock
Uncoated	Fused Silica	7980 0F	50.80	9.53	#38-060	€257,50 Volume Pricing	20+ In Stock
Uncoated	Fused Quartz	-	55.00	1.50	#37-667	€66,95 Volume Pricing	20+ In Stock
Uncoated	Fused Silica	7980 0A	76.20	12.70	#14-844	€515,00 Volume Pricing	Contact Us
Uncoated	Fused Silica	7980 0G	134.00	3.00	#37-668	€200,85 Volume Pricing	3 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com