

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Cylinder Lenses](#) / [Imaging Grade Cylinder Lenses](#)

TECHSPEC® Imaging Grade PCV Cylinder Lenses



- Beam Shaping Grade Specifications
- Used with [TECHSPEC® Imaging Grade PCX Cylinder Lenses](#) for Circularizing Beams
- Negative Focal Length

Common Specifications

Physical & Mechanical Properties

Bevel: Protective as needed	Center Thickness Tolerance (mm): ±0.1
Optical Properties	
Substrate: N-BK7	Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ	Irregularity (P-V) @ 632.8nm: λ/4
Plano Axis Wedge (arcmin): <5	Power Axis Wedge (arcmin): <5

Technical Information

Products

Dia. (mm)	Dimensions (mm)	EFL (mm)	Substrate	Coating	Stock Number	Price	Buy
12.70	-	-25.00	N-BK7	Uncoated	#34-618	€88,58 Volume Pricing	3 In Stock
12.70	-	-50.00	N-BK7	Uncoated	#34-619	€83,95 Volume Pricing	2 In Stock
12.70	-	- 100.00	N-BK7	Uncoated	#34-620	€83,95 Volume Pricing	1 In Stock
12.70	-	-25.00	N-BK7	NIR I (600- 1050nm)	#34-679	€100,94 Volume Pricing	5 In Stock
12.70	-	-50.00	N-BK7	NIR I (600- 1050nm)	#34-680	€94,25 Volume Pricing	Contact Us
12.70	-	- 100.00	N-BK7	NIR I (600- 1050nm)	#34-681	€94,25 Volume Pricing	4 In Stock
12.70	-	-25.00	N-BK7	NIR II (750- 1550nm)	#34-638	€100,94 Volume Pricing	5 In Stock
12.70	-	-50.00	N-BK7	NIR II (750- 1550nm)	#34-639	€94,25 Volume Pricing	4 In Stock
12.70	-	- 100.00	N-BK7	NIR II (750- 1550nm)	#34-640	€94,25 Volume Pricing	5 In Stock
12.70	-	-25.00	N-BK7	VIS 0° (425- 675nm)	#34-659	€100,94 Volume Pricing	7 In Stock
12.70	-	-50.00	N-BK7	VIS 0° (425- 675nm)	#34-660	€94,25 Volume Pricing	1 In Stock
12.70	-	- 100.00	N-BK7	VIS 0° (425- 675nm)	#34-661	€94,25 Volume Pricing	Contact Us
25.40	-	-25.00	N-BK7	Uncoated	#34-621	€106,09 Volume Pricing	1 In Stock

25.40	-	-50.00	N-BK7	Uncoated	#34-622	€100,94 Volume Pricing	5 In Stock
25.40	-	-75.00	N-BK7	Uncoated	#34-623	€100,94 Volume Pricing	2 In Stock
25.40	-	- 100.00	N-BK7	Uncoated	#34-624	€100,94 Volume Pricing	2 In Stock
25.40	-	-25.00	N-BK7	NIR I (600- 1050nm)	#34-682	€122,57 Volume Pricing	3 In Stock
25.40	-	-50.00	N-BK7	NIR I (600- 1050nm)	#34-683	€117,42 Volume Pricing	20+ In Stock
25.40	-	-75.00	N-BK7	NIR I (600- 1050nm)	#34-684	€117,42 Volume Pricing	14 In Stock
25.40	-	- 100.00	N-BK7	NIR I (600- 1050nm)	#34-685	€117,42 Volume Pricing	Contact Us
25.40	-	-25.00	N-BK7	NIR II (750- 1550nm)	#34-641	€122,57 Volume Pricing	7 In Stock
25.40	-	-50.00	N-BK7	NIR II (750- 1550nm)	#34-642	€117,42 Volume Pricing	4 In Stock
25.40	-	-75.00	N-BK7	NIR II (750- 1550nm)	#34-643	€117,42 Volume Pricing	8 In Stock
25.40	-	- 100.00	N-BK7	NIR II (750- 1550nm)	#34-644	€117,42 Volume Pricing	6 In Stock
25.40	-	-25.00	N-BK7	VIS 0° (425- 675nm)	#34-662	€122,57 Volume Pricing	Contact Us
25.40	-	-50.00	N-BK7	VIS 0° (425- 675nm)	#34-663	€117,42 Volume Pricing	Contact Us
25.40	-	-75.00	N-BK7	VIS 0° (425- 675nm)	#34-664	€117,42 Volume Pricing	2 In Stock
25.40	-	- 100.00	N-BK7	VIS 0° (425- 675nm)	#34-665	€117,42 Volume Pricing	3 In Stock

-	12.7 x 12.7	-25.00	N-BK7	Uncoated	#34-758	€94,25 Volume Pricing	20+ In Stock
-	12.7 x 12.7	-50.00	N-BK7	Uncoated	#34-759	€88,58 Volume Pricing	3 In Stock
-	12.7 x 12.7	-25.00	N-BK7	NIR I (600-1050nm)	#35-004	€106,09 Volume Pricing	3 In Stock
-	12.7 x 12.7	-50.00	N-BK7	NIR I (600-1050nm)	#35-005	€100,94 Volume Pricing	Contact Us
-	12.7 x 12.7	-25.00	N-BK7	NIR II (750-1550nm)	#35-016	€112,27 Volume Pricing	4 In Stock
-	12.7 x 12.7	-50.00	N-BK7	NIR II (750-1550nm)	#35-017	€100,94 Volume Pricing	2 In Stock
-	12.7 x 12.7	-25.00	N-BK7	VIS 0° (425-675nm)	#34-992	€106,09 Volume Pricing	3 In Stock
-	12.7 x 12.7	-50.00	N-BK7	VIS 0° (425-675nm)	#34-993	€100,94 Volume Pricing	5 In Stock
-	25.4 x 25.4	-50.00	N-BK7	Uncoated	#34-760	€106,09 Volume Pricing	5 In Stock
-	25.4 x 25.4	-75.00	N-BK7	Uncoated	#34-761	€106,09 Volume Pricing	2 In Stock
-	25.4 x 25.4	-50.00	N-BK7	NIR I (600-1050nm)	#35-006	€122,57 Volume Pricing	Contact Us
-	25.4 x 25.4	-75.00	N-BK7	NIR I (600-1050nm)	#35-007	€122,57 Volume Pricing	1 In Stock
-	25.4 x 25.4	-50.00	N-BK7	NIR II (750-1550nm)	#35-018	€122,57 Volume Pricing	4 In Stock
-	25.4 x 25.4	-75.00	N-BK7	NIR II (750-1550nm)	#35-019	€122,57 Volume Pricing	1 In Stock
-	25.4 x 25.4	-50.00	N-BK7	VIS 0° (425-675nm)	#34-994	€122,57 Volume Pricing	2 In Stock

-	25.4 x 25.4	-75.00	N-BK7	VIS 0° (425- 675nm)	#34-995	€122,57 Volume Pricing	2 In Stock
---	-------------	--------	-----------------------	---------------------------	-------------------------	---	------------



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com