

[All Products](#) / [Optomechanics](#) / [Benchtop Optical Mounts](#) / [Optical Lens and Filter Mounts](#)

Multi-Axis Adjustable Optic Mounts



- 2-Axis, 3-Axis, and 5-Axis Adjustable Mounts Available
- Options for 12.5mm (0.5"), 25mm (1"), and 50mm (2") Dia. Optics
- M6 Mounting Threads

Common Specifications

Physical & Mechanical Properties

Construction:



Black Anodized Aluminum

Threading & Mounting

Compatible Post:

M6 x 1.0

Technical Information



Products

Type	Size of Compatible Optics (mm)	CA (mm)	Travel (mm)	Stock Number	Price	Buy
Adjustable - Linear (XY)	12.5 - 12.7	10.0	±1.5 in X and Y	#62-955	€251,32 Volume Pricing	10 In Stock
Adjustable - Linear (XY)	25.0 - 25.4	22.0	±1.5 in X and Y	#62-956	€265,74 Volume Pricing	14 In Stock
Adjustable - Linear (XY)	50.0 - 50.8	46.0	±2.0 in X and Y	#62-957	€296,64 Volume Pricing	3 In Stock
Adjustable - Linear (XY)	-	1" x 32 TPI	±1.5 in X and Y	#87-209	€356,38 Volume Pricing	4 In Stock
Adjustable - Linear (XYZ)	12.5 - 12.7	10.0	±2.0 in X and Y, ±1.5 in Z	#62-958	€413,03 Volume Pricing	4 In Stock
Adjustable - Linear (XYZ)	25.0 - 25.4	22.0	±2.0 in X and Y, ±1.5 in Z	#62-959	€520,15 Volume Pricing	7 In Stock
Adjustable - Linear (XYZ)	50.0 - 50.8	46.0	±1.5 in X and Y, ±1.5 in Z	#62-960	€581,95 Volume Pricing	5 In Stock
Adjustable - Linear (XYZ)	-	1" x 32 TPI	±2.0 in X and Y, ±1.5 in Z	#87-210	€465,56 Volume Pricing	2 In Stock
Adjustable - Linear (XYZ) & Tip-Tilt	25.0 - 25.4	22.0	±2.0 in X and Y, ±1.5 in Z	#13-776	€726,15 Volume Pricing	2 In Stock
Adjustable - Linear (XYZ) & Tip-Tilt	50.0 - 50.8	46.0	±2.0 in X and Y, ±1.5 in Z	#13-778	€808,55 Volume Pricing	1 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
 Phone: 1-800-363-1992 :
www.edmundoptics.com