


[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Aspheric Lenses](#) / [Glass Polished](#)

TECHSPEC® Near-Infrared (NIR) Aspheric Lenses



- Optimized for Applications in the NIR
- Uncoated or AR coated versions available
- Multiple Design Wavelengths Available

Common Specifications

Physical & Mechanical Properties

Bevel:

Protective as needed

Technical Information

Products

Dia. (mm)	EFL (mm)	Aspheric DWL (nm)	NA	Coating	Stock Number	Price	Buy
10.00	8.00	780	0.63	Uncoated	#13-496	€177,16 Volume Pricing	20+ In Stock
10.00	8.00	780	0.63	VIS+ (350-700nm)	#16-266	€197,76 Volume Pricing	2 In Stock
10.00	8.00	780	0.63	NIR+ (600-1050nm)	#16-278	€197,76 Volume Pricing	20+ In Stock
10.00	8.00	780	0.63	SWIR+ (900-1700nm)	#16-290	€197,76 Volume Pricing	9 In Stock
12.50	25.00	780	0.25	Uncoated	#13-498	€203,94 Volume Pricing	20+ In Stock
12.50	25.00	780	0.25	VIS+ (350-700nm)	#16-268	€224,54 Volume Pricing	15 In Stock
12.50	25.00	780	0.25	NIR+ (600-1050nm)	#16-280	€224,54 Volume Pricing	11 In Stock
12.50	25.00	780	0.25	SWIR+ (900-1700nm)	#16-292	€224,54 Volume Pricing	12 In Stock
12.50	10.00	780	0.63	Uncoated	#13-497	€203,94 Volume Pricing	20+ In Stock
12.50	10.00	780	0.63	VIS+ (350-700nm)	#16-267	€224,54 Volume Pricing	17 In Stock
12.50	10.00	780	0.63	NIR+ (600-1050nm)	#16-279	€224,54 Volume Pricing	13 In Stock
12.50	10.00	780	0.63	SWIR+ (900-1700nm)	#16-291	€224,54 Volume Pricing	8 In Stock
15.00	30.00	1550	0.25	Uncoated	#17-417	€321,36 Volume Pricing	7 In Stock
15.00	30.00	1550	0.25	SWIR+	#29-987	€342,99 Volume Pricing	Contact Us
15.00	30.00	1550	0.25	1550nm V-Coat	#22-937	€342,99 Volume Pricing	1 In Stock
15.00	15.00	2000	0.5	Uncoated	#18-749	€618,00 Volume Pricing	5 In Stock

15.00	15.00	1550	0.5	Uncoated	#17-416	€321,36 Volume Pricing	14 In Stock
15.00	15.00	1550	0.5	SWIR+	#29-986	€342,99 Volume Pricing	8 In Stock
15.00	15.00	1550	0.5	1550nm V-Coat	#22-936	€342,99 Volume Pricing	14 In Stock
15.00	12.00	780	0.63	Uncoated	#13-499	€219,39 Volume Pricing	20+ In Stock
15.00	12.00	780	0.63	VIS+ (350-700nm)	#16-269	€241,02 Volume Pricing	15 In Stock
15.00	12.00	780	0.63	NIR+ (600-1050nm)	#16-281	€241,02 Volume Pricing	8 In Stock
15.00	12.00	780	0.63	SWIR+ (900-1700nm)	#16-293	€241,02 Volume Pricing	11 In Stock
15.00	11.25	1550	0.67	Uncoated	#17-415	€342,99 Volume Pricing	6 In Stock
15.00	11.25	1550	0.67	SWIR+	#29-985	€364,62 Volume Pricing	6 In Stock
15.00	11.25	1550	0.67	1550nm V-Coat	#22-935	€364,62 Volume Pricing	4 In Stock
18.00	15.00	780	0.60	Uncoated	#13-500	€241,02 Volume Pricing	16 In Stock
18.00	15.00	780	0.60	VIS+ (350-700nm)	#16-270	€262,65 Volume Pricing	11 In Stock
18.00	15.00	780	0.60	NIR+ (600-1050nm)	#16-282	€262,65 Volume Pricing	20+ In Stock
18.00	15.00	780	0.60	SWIR+ (900-1700nm)	#16-294	€262,65 Volume Pricing	Contact Us
20.00	17.99	780	0.56	Uncoated	#13-501	€251,32 Volume Pricing	20+ In Stock
20.00	17.99	780	0.56	VIS+ (350-700nm)	#16-271	€272,95 Volume Pricing	20+ In Stock
20.00	17.99	780	0.56	NIR+ (600-1050nm)	#16-283	€272,95 Volume Pricing	4 In Stock
20.00	17.99	780	0.56	SWIR+ (900-1700nm)	#16-295	€272,95 Volume Pricing	20+ In Stock
25.00	50.00	780	0.25	Uncoated	#13-503	€257,50 Volume Pricing	10 In Stock

25.00	50.00	1550	0.25	Uncoated	#17-421	€374,92 Volume Pricing	6 In Stock
25.00	50.00	780	0.25	VIS+ (350-700nm)	#16-273	€289,43 Volume Pricing	14 In Stock
25.00	50.00	780	0.25	NIR+ (600-1050nm)	#16-285	€289,43 Volume Pricing	10 In Stock
25.00	50.00	780	0.25	SWIR+ (900-1700nm)	#16-297	€289,43 Volume Pricing	13 In Stock
25.00	50.00	1550	0.25	SWIR+	#29-990	€406,85 Volume Pricing	8 In Stock
25.00	50.00	1550	0.25	1550nm V-Coat	#22-940	€406,85 Volume Pricing	Contact Us
25.00	25.00	1550	0.5	Uncoated	#17-419	€374,92 Volume Pricing	15 In Stock
25.00	25.00	1550	0.5	SWIR+	#29-989	€406,85 Volume Pricing	5 In Stock
25.00	25.00	1550	0.5	1550nm V-Coat	#22-939	€406,85 Volume Pricing	5 In Stock
25.00	20.00	780	0.63	Uncoated	#13-502	€257,50 Volume Pricing	12 In Stock
25.00	20.00	780	0.63	VIS+ (350-700nm)	#16-272	€289,43 Volume Pricing	12 In Stock
25.00	20.00	780	0.63	NIR+ (600-1050nm)	#16-284	€289,43 Volume Pricing	20+ In Stock
25.00	20.00	780	0.63	SWIR+ (900-1700nm)	#16-296	€289,43 Volume Pricing	20+ In Stock
25.00	15.00	1550	0.83	Uncoated	#17-418	€401,70 Volume Pricing	2 In Stock
25.00	15.00	1550	0.83	SWIR+	#29-988	€433,63 Volume Pricing	20+ In Stock
25.00	15.00	1550	0.83	1550nm V-Coat	#22-938	€433,63 Volume Pricing	14 In Stock
30.00	26.00	780	0.58	Uncoated	#13-504	€337,84 Volume Pricing	20+ In Stock
30.00	26.00	780	0.58	VIS+ (350-700nm)	#16-274	€369,77 Volume Pricing	20+ In Stock
30.00	26.00	780	0.58	NIR+ (600-1050nm)	#16-286	€369,77 Volume Pricing	20+ In Stock

30.00	26.00	780	0.58	SWIR+ (900-1700nm)	#16-298	€369,77 Volume Pricing	5 In Stock
45.00	32.00	780	0.70	Uncoated	#13-505	€471,74 Volume Pricing	13 In Stock
45.00	32.00	780	0.70	VIS+ (350-700nm)	#16-275	€508,82 Volume Pricing	Contact Us
45.00	32.00	780	0.70	NIR+ (600-1050nm)	#16-287	€508,82 Volume Pricing	5 In Stock
45.00	32.00	780	0.70	SWIR+ (900-1700nm)	#16-299	€508,82 Volume Pricing	5 In Stock
50.00	100.00	780	0.25	Uncoated	#13-507	€545,90 Volume Pricing	20+ In Stock
50.00	100.00	780	0.25	VIS+ (350-700nm)	#16-277	€597,40 Volume Pricing	4 In Stock
50.00	100.00	780	0.25	NIR+ (600-1050nm)	#16-289	€597,40 Volume Pricing	20+ In Stock
50.00	100.00	780	0.25	SWIR+ (900-1700nm)	#16-301	€597,40 Volume Pricing	20+ In Stock
50.00	40.00	780	0.63	Uncoated	#13-506	€545,90 Volume Pricing	20+ In Stock
50.00	40.00	780	0.63	VIS+ (350-700nm)	#16-276	€597,40 Volume Pricing	20+ In Stock
50.00	40.00	780	0.63	NIR+ (600-1050nm)	#16-288	€597,40 Volume Pricing	12 In Stock
50.00	40.00	780	0.63	SWIR+ (900-1700nm)	#16-300	€597,40 Volume Pricing	20+ In Stock
75.00	150.00	780	0.25	Uncoated	#13-509	€854,90 Volume Pricing	5 In Stock
75.00	150.00	780	0.25	NIR+ (600-1050nm)	#28-916	€963,05 Volume Pricing	4 In Stock
100.00	100.00	780	0.50	NIR+ (600-1050nm)	#28-917	€1.256,60 Volume Pricing	1 In Stock
75.00	60.00	780	0.63	Uncoated	#13-508	€854,90 Volume Pricing	14 In Stock
75.00	60.00	780	0.63	NIR+ (600-1050nm)	#28-915	€963,05 Volume Pricing	5 In Stock
100.00	200.00	780	0.25	Uncoated	#13-511	€1.153,60 Volume Pricing	5 In Stock

100.00	200.00	780	0.25	NIR+ (600-1050nm)	#28-918	€1.256,60 Volume Pricing	4 In Stock
100.00	100.00	780	0.50	Uncoated	#13-510	€1.153,60 Volume Pricing	20+ In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
 Phone: 1-800-363-1992 :
www.edmundoptics.com