

[See all 44 Products in Family](#)

## 100 x 100mm 220 Grit Ground Glass Diffuser



Stock #45-656 **20+ In Stock**

⊖ 1 ⊕ €52<sup>50</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | €52,50 each                   |
| Qty 11+        | €47,25 each                   |
| Need More?     | <a href="#">Request Quote</a> |

**i** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Ground Glass Diffuser **Type:**

Sandblasted on first surface **Note:**

### Physical & Mechanical Properties

**Dimensional Tolerance (mm):**  
±0.76

|                 |                                       |
|-----------------|---------------------------------------|
| 100.00 x 100.00 | <b>Dimensions (mm):</b>               |
| Seamed          | <b>Edges:</b>                         |
| 220             | <b>Grit:</b> <input type="checkbox"/> |
| 1.60            | <b>Thickness (mm):</b>                |
| 100.00          | <b>Width (mm):</b>                    |
| 100.00          | <b>Length (mm):</b>                   |

## Optical Properties

|             |  |
|-------------|--|
| Uncoated    | <b>Coating:</b>                            |
| Float Glass | <b>Substrate:</b> <input type="checkbox"/> |
| 350 - 2000  | <b>Wavelength Range (nm):</b>              |

## Regulatory Compliance

|                           |                                    |
|---------------------------|------------------------------------|
| <a href="#">Compliant</a> | <b>RoHS 2015:</b>                  |
| <a href="#">View</a>      | <b>Certificate of Conformance:</b> |
| <a href="#">Compliant</a> | <b>Reach 247:</b>                  |


## Product Details

- Available in Sizes Ranging from 5mm Diameter to 250mm Square
- Low Scatter Loss
- Evenly Ground Surface for Even Diffusion
- [Fused Silica Substrates](#) Available

Ground Glass Diffusers are comprised of high tolerance, quality ground glass making them ideal for a variety of industrial applications. The float glass substrate has excellent visible transmission and is ideal for general diffusing applications. A 120-grit, 220-grit or 600-grit (as noted) sandblast is used to create a diffuse surface on the glass. Ground Glass Diffusers have even diffusion across the entire surface from undergoing two orthogonal passes during this sandblast process. The scattering is a compromise of low scatter loss and medium diffusion. Typical applications include use in screens, illuminator diffusion, and targets.

Can't find what you need? Get a quick [custom quote](#).

## Technical Information



[Quote Your Size](#)

[Compatible Mounts](#)