

[All Products](#) / [Optomechanics](#) / [T-Mount Circular Optics](#)

[See all 57 Products in Family](#)

TECHSPEC® 20mm

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: European Union

Submit



1

€59^{,50}

ADD TO CART

Volume Pricing	
Qty 1-4	€59,50 each
Qty 5-9	€52,90 each
Qty 10-25	€49,10 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

- STEP:step
- PDF Drawing:pdf
- IGES:igs
- eDrawing:eprt
- EO Spec Sheet
- [Download All](#)

General

Type: Fixed	Function: Optic Mount (Fixed)
Type of Optics: Circular	

Physical & Mechanical Properties

Extension Length (mm): 14.0	Total Length (mm): 18.0
Min. Thickness of Compatible Optics (mm): 3.5	Max. Thickness of Compatible Optics (mm): 11.0
Clear Aperture CA (mm): 18.00	Construction: Black Anodized Aluminum (6061 T6)
Outer Diameter (mm): 30.0	

Threading & Mounting

Thread Type: C-Mount	Diameter of Compatible Optics (mm): 20.0
-----------------------------	---

Regulatory Compliance

RoHS 2015: Compliant	Certificate of Conformance: View
REACH 241: Compliant	

Product Details

- Mounts for Simple Lenses, Achromats, Filters, and Mirrors
- Designed to Integrate with Any C, S, or T-Mount Circular Optic Mount
- Optic is Held in Place with Included Retainer Ring

TECHSPEC® C, S, and T-Mount Circular Optic Mounts are designed to integrate with a wide variety of Edmund Optics compatible systems. An included threaded retainer ring, designed to accept a standard spanner, holds the optic in place. These optomechanical components utilizing C, S, or T-Mount Circular Optic Mounts are threaded for 1" x 32TPI, M12 x 0.5, or M42 x 0.75 mm. They are ideal for creating and personalization of a diverse range of optical systems.

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Note: #56-353, #56-354, #52-933, and #52-292 are all 3-part assemblies

compatible systems. An included threaded retainer ring, designed to accept a standard spanner, holds the optic in place. These optomechanical components utilizing C, S, or T-Mount Circular Optic Mounts are threaded for 1" x 32TPI, M12 x 0.5, or M42 x 0.75 mm. They are ideal for creating and personalization of a diverse range of optical systems.

Technical Information

Accessories

Note: Compatible accessories for individual stock numbers may vary. If unsure about which accessories work with your products, please contact us [here](#).

	Title	Compare	Stock Number	Price	Buy
MORE+	C-Mount Male to T-Mount Female Step-Up Adapter		#53-483	€62,50 Volume Pricing Request Quote	20+ In Stock <input type="text" value="1"/>
MORE+	C-Mount Female to T-Mount Male Step-Down Adapter		#58-753	€62,50 Volume Pricing Request Quote	CONTACT US <input type="text" value="1"/>
MORE+	C-Mount Female to SM1 Male Step-Down Adapter		#88-954	€59,50 Volume Pricing Request Quote	20+ In Stock <input type="text" value="1"/>
MORE+	C-Mount Male to SM1 Female Step-Up Adapter		#88-955	€62,50 Volume Pricing Request Quote	20+ In Stock <input type="text" value="1"/>
MORE+	S-Mount Female to C-Mount Male Step-Down Adapter		#63-945	€59,50 Volume Pricing Request Quote	20+ In Stock <input type="text" value="1"/>
MORE+	S-Mount Male to C-Mount Female Step-Up Adapter		#63-974	€62,50 Volume Pricing Request Quote	20+ In Stock <input type="text" value="1"/>
MORE+	S-Mount Female to SM05 Male Step-Down Adapter		#88-952	€62,50 Volume Pricing Request Quote	7 In Stock <input type="text" value="1"/>
MORE+	S-Mount Male to SM05 Female Step-Up Adapter		#88-953	€62,50 Volume Pricing Request Quote	17 In Stock <input type="text" value="1"/>
MORE+	M29 x 0.75 Male to C-Mount Female Step-Down Adapter		#11-177	€39,50 Volume Pricing Request Quote	20+ In Stock <input type="text" value="1"/>
MORE+	C-Mount Male to M29 x 0.75 Male Adapter		#11-178	€39,50 Volume Pricing Request Quote	6 In Stock <input type="text" value="1"/>

Related Products



C, S, and T-Mount Ring Mounts



Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:



Multi-Element Inner Single Optic Mounts

Frequently Purchased Together



#03-629 - C-Mount Double Male Thread Ring
€36,75

Qty



#03-625 - 30mm - 50mm Length, C-Mount Fine Focus Tube
€118,00

Qty



#03-627 - C-Mount Male to Olympus (RMS/DIN) Female Step-Down Adapter
€52,00

Qty



#03-618 - 5mm Spacer to convert CS-Mount Cameras to C-Mount
€29,00

Qty

Resources

Media Type

- Application Note
- Video
- FAQ
- Glossary
- Trending in Optics

APPLICATION NOTE

A Closer Look at Kinematic Movement

VIDEO

E-Series Kinematic Optical Mirror Mounts

VIDEO

TECHSPEC® 90° Kinematic Adapter

VIDEO

Important Concepts for Selecting Optical...

FAQ

How do truncated optics eliminate the...

GLOSSARY

Gimbal

[View More](#)

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: