

25mm MPT Series 1.4", 45MP Fixed Focal Length Lens



25mm MPT Series 1.4", 45MP Fixed Focal Length Lens

Stock **#25-762** [CONTACT US](#)

-

1

+

€1.058⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.058,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Series:	Computar MPT Series Fixed Focal Length Lenses
Model Number:	F2524-MPT
Type:	Fixed Focal Length Lens
Physical & Mechanical Properties	
Iris Option:	

Manual Iris	
Length (mm):	70.30
Outer Diameter (mm):	39
Weight (g):	152

Dimensions (mm):	39.0 x 70.3
------------------	-------------

Optical Properties

Horizontal Field of View, 1.2" Sensor:	32.7° x 28.5° (D 42.4°)
--	-------------------------

Horizontal Field of View, 1.1" Sensor:	31.8° x 23.6° (D 39.0°)
--	-------------------------

Maximum Image Circle (mm):	23.10
----------------------------	-------

Focal Length FL (mm):	25.00
-----------------------	-------

Working Distance (mm):	150 - ∞
------------------------	---------

Aperture (f/#):	f/2.6 - f/16
-----------------	--------------

Distortion (%):	0.06
-----------------	------

Maximum Distortion (%):	0.06
-------------------------	------

Lens Wavelength Range:	VIS
------------------------	-----

Sensor

Maximum Sensor Format:	1.4"
------------------------	------

Resolution (Megapixels):	45.00
--------------------------	-------

Pixel Size (µm):	2.74
------------------	------

Threading & Mounting

Filter Thread:	M34.0 x 0.75
----------------	--------------

Mount:	C-Mount
--------	---------

Environmental & Durability Factors

Operating Temperature (°C):	-10°C to +50°C
-----------------------------	----------------

Regulatory Compliance

Certificate of Conformance:	View
-----------------------------	----------------------

Product Details

- Ultra-Low Distortion
- Compatible with 45 MegaPixel, 1.4", C-Mount Cameras
- Focal Lengths Ranging from 12mm – 50mm

Computar MPT Series Fixed Focal Length Lenses are engineered to provide a high 45 MegaPixel resolution while maintaining exceptionally low-distortion on large 1.4" imaging sensors such as the Sony IMX350. These lightweight, compact C-Mount lenses are available in focal lengths of 12mm, 16mm, 25mm, 35mm, and 50mm. Field curvature and astigmatism are corrected by positioning the high refractive index glass and low partial dispersion glass at crucial locations. Computar MPT Series Fixed Focal Length Lenses offer high-level aberration correction and precision alignment enabling extraordinary performance across the full 1.4" format sensor. These lenses are ideal for the use in machine vision, factory automation, and wide-area surveillance applications.