

[See all 103 Products in Family](#)

# IDS U3-34L0XCP-M-GL, USB 3.0, 1/1.6" Monochrome Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ USB3 Cameras



Stock #78-287 **1 In Stock**

- 1 + €358.<sup>00</sup>

**ADD TO CART**

Volume Pricing

Qty 1+	€358,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

Monochrome **Spectrum:**

**General**

Monochrome Camera **Type:**

U3-34L0XCP-M-GL **Model Number:**

IDS Imaging Development Systems **Manufacturer:**

uEye+ XCP **Camera Series:**

## Physical & Mechanical Properties

29 x 29 x 17 (excludes connectors and lens mount) **Dimensions (mm):**

62 **Weight (g):**

Full **Housing:**

## Sensor

Not Specified **Image Buffer:**

1/1.6" **Sensor Format:**

12.62 **Resolution (Megapixels):**

40.00 **Frame Rate (fps):**

3,552 x 3,552 **Pixels (H x V):**

2.00 x 2.00 **Pixel Size, H x V (µm):**

7.104 x 7.104 **Sensing Area, H x V (mm):**

Sony IMX676 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Rolling **Shutter Type:**

12 bit **Pixel Depth:**

0.031ms - 2000ms **Exposure Time:**

68.00 **Dynamic Range (dB):**

USB3 Vision **Machine Vision Standard:**

## Electrical

1 - 1.3 **Power Consumption (W):**

## Hardware & Interface Connectivity

USB 3.0 **Interface:**

USB 3.0 micro-B, screwable **Connector:**

Power over USB **Power Supply:**

8-pin connector **GPIO Connector Type:**

## Threading & Mounting

C-Mount **Mount:**

## Environmental & Durability Factors

0 to +55 **Operating Temperature (°C):**

-20 to +60 **Storage Temperature (°C):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Standard (SE), Compact (CP), and Ultra Compact (XCP) Housing Options Available
- C-Mount with Large Format CMOS Sensors up to 1.1"
- Up to 20.44MP Resolution with Framerrates up to 396fps

IDS Imaging uEye CP/XCP/SE USB3 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GeniCam and USB3 Vision standards for easy software development and integration. The CP cameras are the industry standard size of 29 x 29 x 29mm and work for almost any application. The XCP cameras have an ultra-compact size of 29 x 29 x 17mm and are an excellent option for price-sensitive, single-camera applications. The SE cameras have a larger housing size of 34 x 44 x 47mm to allow for exceptional heat management and are ideal for noise and heat-sensitive applications. IDS Imaging uEye CP/XCP/SE USB3 Cameras are ideal for manufacturing, industrial, and automation applications.

---

;