

[See all 103 Products in Family](#)

IDS U3-38L1XLS-C, USB 3.0, 1/2.3" Color Board Level Camera

See More by [IDS Imaging Development Systems](#)



Pictured is an example of an IDS Board Level Camera (Front)



Stock #78-255 [CONTACT US](#)

- 1 + €284.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€284,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

Color **Spectrum:**

General

Color Camera **Type:**

U3-38L1XLS-C **Model Number:**

IDS Imaging Development Systems **Manufacturer:**

uEye+ XLS **Camera Series:**

Physical & Mechanical Properties

32.5 x 32.5 x 14 (excludes connectors and lens mount) **Dimensions (mm):**

13 **Weight (g):**

Board Level **Housing:**

Sensor

Not Specified **Image Buffer:**

1/2.3" **Sensor Format:**

12.33 **Resolution (Megapixels):**

18.00 **Frame Rate (fps):**

4,056 x 3,040 **Pixels (H x V):**

1.55 x 1.55 **Pixel Size, H x V (µm):**

6.287 x 4.712 **Sensing Area, H x V (mm):**

Sony IMX412 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Rolling **Shutter Type:**

12 bit **Pixel Depth:**

0.032ms - 1900ms **Exposure Time:**

68.00 **Dynamic Range (dB):**

USB3 Vision **Machine Vision Standard:**

Electrical

0.5 - 1 **Power Consumption (W):**

Hardware & Interface Connectivity

USB 3.0 **Interface:**

USB 3.0 micro-B **Connector:**

Power over USB **Power Supply:**

8-pin connector **GPIO Connector Type:**

Threading & Mounting

S-Mount (M12 x 0.5) **Mount:**

Environmental & Durability Factors

0 to +75 **Operating Temperature (°C):**

-20 to +80 **Storage Temperature (°C):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Standard (SE), Compact (CP), and Ultra Compact (XCP) Housing Options Available
- C-Mount with Large Format CMOS Sensors up to 1.1"
- Up to 20.44MP Resolution with Framerrates up to 396fps

IDS Imaging uEye CP/XCP/SE USB3 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GeniCam and USB3 Vision standards for easy software development and integration. The CP cameras are the industry standard size of 29 x 29 x 29mm and work for almost any application. The XCP cameras have an ultra-compact size of 29 x 29 x 17mm and are an excellent option for price-sensitive, single-camera applications. The SE cameras have a larger housing size of 34 x 44 x 47mm to allow for exceptional heat management and are ideal for noise and heat-sensitive applications. IDS Imaging uEye CP/XCP/SE USB3 Cameras are ideal for manufacturing, industrial, and automation applications.

;