

[See all 119 Products in Family](#)

LUCID Vision Labs Phoenix™ PHX016S-CC-IX, Sony IMX273, 1.6 MP, Color Camera

See More by [LUCID Vision Labs™](#)



LUCID Vision Labs Phoenix™ Power over Ethernet (PoE) Cameras



Stock **#13-656** [CONTACT US](#)

[Similar Cameras](#)

-

1

+

€335^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€335,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

Color

Spectrum:

General

Color Camera

Type:

PHX016S-CC-IX	Model Number:
Lucid Vision Labs	Manufacturer:
Phoenix™	Camera Series:

Physical & Mechanical Properties

24 x 24 x 27.35 (excludes connectors and lens mount)	Dimensions (mm):
30	Weight (g):
Partial	Housing:

Sensor

128MB	Image Buffer:
1/2.9"	Sensor Format:
1.60	Resolution (Megapixels):
77.00	Frame Rate (fps):
1,440 x 1,080	Pixels (H x V):
3.45 x 3.45	Pixel Size, H x V (µm):
4.97 x 3.73	Sensing Area, H x V (mm):
Sony IMX273	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
12 bit	Pixel Depth:
30µs - 10s	Exposure Time:
71.34	Dynamic Range (dB):
GigE Vision v2.0	Machine Vision Standard:

Electrical

2.5 (External Power Supply) 3.1 (PoE)	Power Consumption (W):
--	------------------------

Hardware & Interface Connectivity

GigE (PoE)	Interface:
GigE, ix Industrial®	Connector:
Power over Ethernet (PoE) or via GPIO with 12-24VDC Power Supply	Power Supply:
1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional ports	GPIOs:
Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588)	Synchronization:
Back Panel	Interface Port Orientation:
8-pin JST	GPIO Connector Type:

Threading & Mounting

C-Mount	Mount:
¼-20 with Tripod Mount Adapter #11-474	Mounting Threads:

Environmental & Durability Factors

Operating Temperature (°C):	
-20 to +55	
Storage Temperature (°C):	
-30 to +60	

Regulatory Compliance

RoHS 2015:	
Exempt	
Certificate of Conformance:	
View	

Reach 247:	
Contains SVHC(s)	

Product Details

- Unfolding Board Stacks for Customization
- Power Over Ethernet (PoE) for Easy Integration
- Compact Size Starting at 24 x 24mm

LUCID Vision Labs Phoenix™ Power over Ethernet (PoE) Cameras are compact, high performance cameras with one of the smallest form factors in the PoE GigE market. Featuring unfolding board stacks, these cameras easily transform between a 90° and 180° angle shape to provide flexible system integration. Additional software versatility is provided by GigE Vision compliancy, allowing for compatibility with third-party GigE Vision software. LUCID Vision Labs Phoenix™ Power over Ethernet (PoE) Cameras offer powerful Image Signal Processing (ISP), ensuring optimal camera performance with options including Region of Interest (ROI), Color Correction Matrix (CCM), and Binning without any limitations on higher frame rates. These cameras are ideal for industrial applications requiring cameras with compact form factors.

Note: GigE cable required for operation, both RJ45 and ix™ versions are available. The ix™ is an miniaturized industrial connector that is not compatible with RJ45 cables. Optional tripod adapter ([#11-474](#)) available.