


[See all 9 Products in Family](#)

Lumenera INFINITY 8-3C Microscopy Color Camera

See More by [Teledyne Lumenera](#)



Stock **#25-351** [CONTACT US](#)

-

1

+

€3.500⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€3.500,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

Color	Spectrum:
-------	-----------

General

Color Microscopy Camera	Type:
i8-LC00-03M	Model Number:

Teledyne Lumenera	Manufacturer:
INFINITY	Camera Series:
Physical & Mechanical Properties	
41.5 x 45 x 45 (includes lens mount)	Dimensions (mm):
108	Weight (g):
Full	Housing:
Sensor	
128MB	Image Buffer:
2/3"	Sensor Format:
2.90	Resolution (Megapixels):
62.00	Frame Rate (fps):
1,944 x 1,472	Pixels (H x V):
4.5 x 4.5	Pixel Size, H x V (µm):
8.75 x 6.62	Sensing Area, H x V (mm):
Sony IMX429	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
8/12 bit	Pixel Depth:
72	Dynamic Range (dB):
Electrical	
2.3 - 3.6	Power Consumption (W):
Hardware & Interface Connectivity	
USB 3.1	Interface:
Power over USB	Power Supply:
Not Specified	GPIOs:
Hardware Trigger (GPIO)	Synchronization:
Side Panel	Interface Port Orientation:
9-pin Hirose (JST)	GPIO Connector Type:
Threading & Mounting	
C-Mount	Mount:
M3x0.5 (Integrated into Housing)	Mounting Threads:
Environmental & Durability Factors	
0 to +50	Operating Temperature (°C):
-30 to +70	Storage Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Exceptional Low Light Sensitivity
- Ideal for Life Sciences, Clinical, and Industrial Applications
- Affordable Price Point with Included Microscopy Software



Teledyne Lumenera INFINITY8 Microscopy Cameras offer an affordable solution for low light imaging in a compact form factor. Featuring low noise and large pixels, these cameras are ideal for a wide range of lighting conditions including the low light levels common in fluorescence imaging. Available with 1/1.8", 2/3", and 1" sensor sizes and megapixel range of 2 – 20 MP, each camera is compatible with Windows and Mac operating systems. Teledyne Lumenera INFINITY8 Microscopy Cameras include an INFINITY ANALYZE 7 software license, for camera operation and immediate analysis of the imaging results, and 3m Micro-B to Type-A USB cable.