

[All Products](#) / [Optomechanics](#) / [Pedestal Posts and Accessories](#)

[See all 62 Products in Family](#)

76.2mm Pedestal Post

5 Pack

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: European Union

[Submit](#)



Pedestal Post

- 1 +

€202⁰⁰

[ADD TO CART](#)

Volume Pricing	
Qty	€202,00
1+	each
Need More?	Request Quote

Product Downloads
EO Spec Sheet

! Prices shown are exclusive of VAT/local taxes

General

Type: Metric	Contents of Kit: 5X #15-843, 5X #15-859
Note: With M6x1.0 screw holes on the base	Function: Pedestal Post

Physical & Mechanical Properties

Length (mm): 76.20	Construction: Stainless Steel
Weight (kg): 0.31	Post Diameter (mm): 25.4
Base Diameter (mm): 31.5	

Threading & Mounting

Mounting Threads: M4x0.7	
---------------------------------	--

Regulatory Compliance

RoHS 2015: Compliant	Certificate of Conformance: View
Reach 233: Compliant	

Product Details







- 1" Diameter Posts with Metric and English Mounting Hole Options
- Stainless Steel Construction for High Stability
- 0.5"- 4.0" Heights Available
- Refer to the Technical Information Tab to Find the Right Adapter for your Optical Mount and Application






Pedestal Posts and Accessories offer a stable way to mount optical components to a lab table with a consistent mounting height, providing predictable and repeatable mounting of components within an optical system. A variety of pedestal extenders and shim plates are available to ensure that the optical axis height is consistent for all mounted components. Pedestal Posts feature M4 x 0.7 or 8-32 tapped holes on the top surface, compatible with [TECHSPEC® Kinematic Mounts](#), [E-Series Kinematic Mounts](#), [Compact Mirror Mounts](#), and many other [optical mounts](#). M6 x 1.0 or ¼"-20 tapped holes on the bottom surface make these Pedestal Posts directly mountable to Edmund Optics [stages](#) and [breadboards](#). For more compact table mounting, use the Compact Mounting Clamps ([#16-335](#)).

Note: Optical Mount Adapters are available to ensure consistent optical axis height and mounting hole compatibility with Edmund Optics' Optical Mounts. Refer to the Technical Information tab to find the right adapter for your application.

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.






Select Your Country/Region:

Compatible Optic Mount	Optical Size	Mount Stock Number	Extension Length (mm)	Extender Stock Number for English Pedestals	Extender Stock Number for Metric Pedestals
 <p>Optic Component Mount</p>	50mm Dia.	#64-567	16.8	#16-321	#16-315
	2"/50.8mm Dia.	#64-569	16.8	#16-324	#16-587
 <p>Bar-Type Lens / Filter Holder</p>	1"/25.4mm Dia	#03-676	18	#16-325	#16-588
	2 axis: 2"/50.8mm Dia.	#62-957	8	#16-317	#16-311
	3 axis: 1"/25.4mm Dia.	#62-959	18	#16-222	#16-316
	5 axis: 1"/25.4mm Dia.	#13-776	18	#16-222	#16-316
	2"/50.8mm Dia.	#03-669	11	#16-323	#16-586
	2"/50.8mm Dia.	#55-530	16	#16-320	#16-314
 <p>Multi-Axis Adjustable Optic Mounts</p>	2 axis: 1"/25.4mm Dia.	#62-956	20.8	#16-460	#16-459
 <p>Retangular Bar Clamp</p>	2"/50.8mm Sq.	#54-995	11	#16-318	#16-312
 <p>Filter Mount</p>	2"/50.8mm Sq.	#54-997	14	#16-319	#16-313
 <p>Multiple Filter Holder</p>	30mm Dia.	#55-006	16	#16-320	#16-314

	2"/5				#5-320	#16-314
<p>Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.</p> <p>Select Your Country/Region:</p>						
	25mm Cube	#55-013	18		#16-322	#16-316
	50mm Cube	#53-027	18		#16-325	#16-588
	1"/25.4mm Dia.	#55-011	18		#16-322	#16-316
	2"/50.8mm Dia.	#56-329	8		#16-317	#16-311
	1"/25.4mm Dia.	#55-456	14		#16-319	#16-313
	2"/50.8mm Dia.	#55-000	11		#16-318	#16-312

Accessories

Note: Compatible accessories for individual stock numbers may vary. If unsure about which accessories work with your products, please contact us [here](#).

	Title	Compare	Stock Number	Price	Buy
MORE+	Pedestal Extender Kit, English		#17-510 CLEARANCE	€325,50 Request Quote	CONTACT US 1 
MORE+	Pedestal Extender Kit, Metric		#17-511 CLEARANCE	€325,50 Request Quote	CONTACT US 1 
MORE+	Pedestal Post Shim Kit		#17-512 CLEARANCE	€337,00 Request Quote	CONTACT US 1 
MORE+	Pedestal Compact Clamps (1 set of 2)		#16-335	€24,25 Volume Pricing Request Quote	5 In Stock 1 
MORE+	Clamping Fork		#15-859	€11,00 Volume Pricing Request Quote	20+ In Stock 1 

	Title	Compare	Stock Number	Price	Buy
MORE+	12.5mm Length 1/4"-20 #8-32 Thread Adapter			€19,00	7 In Stock <input type="text" value="1"/>
MORE+	15.0mm Length 1/4"-20 #8-32 Thread Adapter				4 In Stock <input type="text" value="1"/>
MORE+	12.5mm Length M6, M4 Thread Adapter		#16-327	€19,00 Volume Pricing Request Quote	6 In Stock <input type="text" value="1"/>
MORE+	15.0mm Length M6, M4 Thread Adapter		#16-328	€22,50 Volume Pricing Request Quote	5 In Stock <input type="text" value="1"/>
MORE+	12.5mm Length M6, #8-32 Thread Adapter		#16-330	€19,00 Volume Pricing Request Quote	14 In Stock <input type="text" value="1"/>
MORE+	15.0mm Length M6, #8-32 Thread Adapter		#16-331	€22,50 Volume Pricing Request Quote	5 In Stock <input type="text" value="1"/>
MORE+	Pedestal Shim 1/4" (6.35mm)		#16-303	€11,25 Volume Pricing Request Quote	6 In Stock <input type="text" value="1"/>
MORE+	Pedestal Shim 3/16" (4.76mm)		#16-304	€10,75 Volume Pricing Request Quote	9 In Stock <input type="text" value="1"/>
MORE+	Pedestal Shim 5/32" (3.97mm)		#16-305	€10,00 Volume Pricing Request Quote	9 In Stock <input type="text" value="1"/>
MORE+	Pedestal Shim 1/8" (3.18mm)		#16-306	€9,50 Volume Pricing Request Quote	9 In Stock <input type="text" value="1"/>
MORE+	Pedestal Shim 3/32" (2.38mm)		#16-307	€8,75 Volume Pricing Request Quote	3 In Stock <input type="text" value="1"/>
MORE+	Pedestal Shim 1/16" (1.59mm)		#16-308	€8,25 Volume Pricing Request Quote	9 In Stock <input type="text" value="1"/>
MORE+	Pedestal Shim 1/32" (0.79mm)		#16-309	€7,50 Volume Pricing Request Quote	7 In Stock <input type="text" value="1"/>
MORE+	Pedestal Shim 1/64" (0.40mm)		#16-310	€7,00 Volume Pricing Request Quote	9 In Stock <input type="text" value="1"/>

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Related Products



English and Metric Breadboards



E-Series Kinematic Optical Mirror Mounts



Multi-Axis Adjustable Optic Mounts

Frequently Purchased Together



#54-640 – 600mm x 200mm,
Breadboard
€298,00

Qty

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:



#54-687 – 160mm x 100mm x 12mm
Metric Lab Jack
€1.000,00

Qty



#58-953 – 63.5mm Length, M4
Stud, Steel Post
€8,95

Qty



#59-757 – 25.4mm Length, M6 Stud,
Steel Post
€8,95

Qty

Resources

Media Type

- FAQ
- Glossary
- Application Note
- Trending in Optics
- Video

? FAQ
Do you have any components that would...

? FAQ
Do your iris diaphragms have mounts for...

GLOSSARY
Axial Runout

GLOSSARY
Concentricity

GLOSSARY
Inverted Load Capacity

GLOSSARY
Tangent Arm Drive

[View More](#)