

## Ring Mount with 0.5" Inner Diameter (ID)



Ring Mounts

Stock #54-265 **17 In Stock**

€29<sup>25</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€29,25 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

**Type:**  
 Mounting Adapter  
**Inner Diameter (inches):**  
 0.5

### Physical & Mechanical Properties

**Construction:**  
 Black Anodized Aluminum  
**Outer Diameter (inches):**

1.25

Thickness (inches):

0.375

### Threading & Mounting

Mounting Threads:

1/4-20

### Regulatory Compliance

RoHS 2015:

Compliant

Reach 224:

Compliant

Certificate of Conformance:

[View](#)

## Product Details


- Swivel Arm for Added Flexibility
- 90° Angle Mounts Connect Horizontal Arms onto Vertical Posts
- Ring Mounts for Increased Versatility
- [Imaging System Bases](#), [Rack and Pinion Focusing Mounts](#), and [Stainless Steel Posts](#) Also Available

Accessories for Imaging Systems are available to increase the versatility of an imaging system. Products in this family include a swivel arm, Infinity Microscope, 90° angle mount, and ring mounts. The swivel arm adds an axis of rotation to the rack and pinion-focusing mounts. The swivel arm can rotate around a vertical post, and the rack and pinion focus mount can rotate around the 1/4" post attached to the swivel arm. The Infinity microscope mounting adapter is compatible with Rack and Pinion Mount #39-357 and reduces the thru hole diameter to 58mm. The 90° angle mount, offered in Accessories for Imaging Solutions, allows the mounting of posts at 90° in optical systems. Ring mounts are available for attaching light sources, articulating arms, straight posts, or any 1/4-20 accessory to standard mounting hardware.

### Features

90° Angle Mount #39-355 features two 3/4" thru holes at 90° with locking knobs. All Ring Mounts feature 1/4-20 mounting hole, set screw for securing post, or optical component within the inner diameter. Swivel Arm #03-684 features a 0.75" diameter post which accepts rack and pinion focusing mount and allows swivel movement. Infinity Mounting Adapter #39-358 features male and female T-thread to replace 24mm tube section of infinity lens.

## Technical Information



Stock No.	A	T	O.D.	I.D.
<a href="#">#54-263</a>	0.375"	0.5"	2.5"	1.5"
<a href="#">#54-264</a>	0.375"	0.5"	1.75"	0.75"
<a href="#">#54-265</a>	0.271"	0.375"	1.25"	0.5"

