

## SugarCUBE™ RS232 Cable



SugarCUBE™ RS232 Cable (#66-034)

Stock **#66-034** **2 In Stock**

⊖ 1 ⊕ €35<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€35,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

Accessory **Type of Illumination:**

#### Regulatory Compliance

**Compliant** **RoHS 2015:**

**Compliant** **Reach 224:**

## Product Details

- Direct Replacement for 150W Halogen Illuminators
- 50% Power Savings Compared To Halogen Source
- More than 60,000 Hour LED Lifetime
- For Use with [Fiber Optic Light Guides](#)

SugarCUBE™ LED Illuminators have an output of up to 1700 lumens and are ideal replacements for standard halogen illuminators because LED illuminators last up to 60 times longer than halogen bulbs and never need to be replaced. These illuminators are controllable manually through controls on the front of the unit or via RS-232 for easy integration into computer controlled systems. Optional, easy-to-operate software is also available.

Available with red, green, blue, white, or white options, SugarCUBE™ LED Illuminators fulfill a wide range of machine vision applications. The standard white unit offers an output power of greater than 1450 lumens and a radiant flux of 1200mW. A fiber optic adapter required to connect a light guide to the illuminator.

## Technical Information

Stock Number	Description	Shoulder Diameter (Inches)	Ferrule Diameter (Inches)	Compatible Illuminator	Compatible Light Guide
<a href="#">#66-301</a>	SugarCUBE™ Light Guide Adapter - 50	0.752	0.564	Red, Green, Blue, White, Ultra White	<a href="#">54-210</a> , <a href="#">39-826</a> , <a href="#">58-839</a> , <a href="#">54-174</a> , <a href="#">38-659</a> , <a href="#">39-369</a> , <a href="#">39-370</a> , <a href="#">39-371</a> <b>Ultra White MUST use liquid light guides</b>
<a href="#">#66-302</a>	SugarCUBE™ Light Guide Adapter - 52	0.877	0.564	Red, Green, Blue, White, Ultra White	<a href="#">54-210</a> , <a href="#">39-826</a> , <a href="#">58-839</a> , <a href="#">54-174</a> , <a href="#">38-659</a> , <a href="#">39-369</a> , <a href="#">39-370</a> , <a href="#">39-371</a> <b>Ultra White MUST use liquid light guides</b>
<a href="#">#66-303</a>	SugarCUBE™ Light Guide Adapter - 53	1.505	0.439	Red, Green, Blue, White	
<a href="#">#66-304</a>	SugarCUBE™ Light Guide Adapter - 56	0.207	0.19	Red, Green, Blue, White	<a href="#">54-199</a> , <a href="#">42-344</a> , <a href="#">39-365</a> , <a href="#">42-345</a> , <a href="#">40-644</a> , <a href="#">39-366</a>
<a href="#">#66-305</a>	SugarCUBE™ Light Guide Adapter - 57	0.255	0.19	Red, Green, Blue, White	<a href="#">54-199</a> , <a href="#">42-344</a> , <a href="#">39-365</a> , <a href="#">42-345</a> , <a href="#">40-644</a> , <a href="#">39-366</a>
<a href="#">#66-306</a>	SugarCUBE™ Light Guide Adapter - 58	0.424	0.314	Red, Green, Blue, White	<a href="#">54-202</a> , <a href="#">53-045</a> , <a href="#">40-639</a> , <a href="#">42-346</a> , <a href="#">42-347</a> , <a href="#">39-367</a> , <a href="#">39-368</a> , <a href="#">53-689</a> , <a href="#">53-692</a> , <a href="#">53-690</a> , <a href="#">53-693</a> , <a href="#">53-691</a> , <a href="#">53-694</a>
<a href="#">#66-307</a>	SugarCUBE™ Light Guide Adapter - 65	1.52	0.63	Red, Green, Blue, White	<a href="#">54-212</a>
<a href="#">#66-308</a>	SugarCUBE™ Light Guide Adapter - 66	1.52	0.565	Red, Green, Blue, White	<a href="#">54-210</a> , <a href="#">39-826</a> , <a href="#">58-839</a> , <a href="#">54-174</a> , <a href="#">38-659</a> , <a href="#">39-369</a> , <a href="#">39-370</a> , <a href="#">39-371</a>
<a href="#">#13-536</a>	SugarCUBE™ Light Guide Adapter - 3mm	0.57	0.314	Red, Green, Blue, White, Ultra White	<a href="#">54-202</a> , <a href="#">53-045</a> , <a href="#">40-639</a> , <a href="#">42-346</a> , <a href="#">42-347</a> , <a href="#">39-367</a> , <a href="#">39-368</a> , <a href="#">53-689</a> , <a href="#">53-692</a> , <a href="#">53-690</a> , <a href="#">53-693</a> , <a href="#">53-691</a> , <a href="#">53-694</a> <b>Ultra White MUST use liquid light guides</b>
<a href="#">#13-537</a>	SugarCUBE™ Light Guide Adapter - 5mm	0.455	0.314	Red, Green, Blue, White, Ultra White	<a href="#">54-202</a> , <a href="#">53-045</a> , <a href="#">40-639</a> , <a href="#">42-346</a> , <a href="#">42-347</a> , <a href="#">39-367</a> , <a href="#">39-368</a> , <a href="#">53-689</a> , <a href="#">53-692</a> , <a href="#">53-690</a> , <a href="#">53-693</a> , <a href="#">53-691</a> , <a href="#">53-694</a> <b>Ultra White MUST use liquid light guides</b>