

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #64-533

CONTACT US



1



€68,50

ADD TO CART

Qty 1-10

€68,50

Qty 11+

€60,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):

0.50 +0.00/-0.01

Effective Focal Length EFL (mm):

0.45

Substrate: ☐

Aluminosilicate Glass Embedded with Silver Ions

f/#:

0.9
Numerical Aperture NA: 0.54
Coating: BBAR (640-700nm)
Type: Gradient Index Lens
Clear Aperture (%) : 90.00
Coating Specification: R _{avg} <0.5% @ 670nm ±30nm
Focal Length Specification Wavelength (nm): 670.00
Gradient Constant (mm⁻¹): 1.363
Index of Refraction n_d - Center of Lens: 1.629
Length (mm): 1.15
Pitch: 0.25
Surface Quality: 40-20
Working Distance (mm): 0
Working Distance Tolerance (mm): ±0.01
Length Tolerance (%) : ±5

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View