

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Gorilla® Glass Windows

Stock #83-367 □ In Stock



1



€52,50

ADD TO CART

Qty 1-5

€52,50

Qty 6+

€40,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Bevel:
Protective as needed

Chemical Strengthening Cycle (hours):
8

Clear Aperture (%):
90.00

Clear Aperture CA (mm): 90.00 x 90.00
Dimensions (mm): 100.00 x 100.00
Thickness (mm): 1.10 (nominal)
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.58 (0 to +300°C)
Density (g/cm³): 2.39
Edges: Fine Ground
Index of Refraction n_d: 1.5
Poisson's Ratio: 0.22
Substrate: Gorilla® Glass
Surface Quality: 80-50
Type: Protective Window
Wavelength Range (nm): 350 - 2200
Young's Modulus (GPa): 70
Length (mm): 100.00
Width (mm): 100.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant