

100mm Dia x 300mm Focal Length, PCX Condenser Lens



Stock #27-502 3-4 DAYS

- 1 + **€83,00**

ADD TO CART

Qty 1-10
€83,00

Qty 11+
€73,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
100.00 +0.0/-0.5

Effective Focal Length EFL (mm):
300.00 @ 587.6nm

Back Focal Length BFL (mm):
291.00

Coating:

Uncoated
Substrate: N-BK7
Surface Quality: 120-80
Center Thickness CT (mm): 12.50
Edge Thickness ET (mm): 4.21
Radius R₁ (mm): 155.00
Clear Aperture CA (mm): 97
f/#: 3
Numerical Aperture NA: 0.17
Type: Condenser Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View