

**TECHSPEC® 10mm Dia x 30mm FL NIR I Coated, Illumination Grade PCX Cylinder Lens**



Stock **#69-708** 3-4 DAYS

- 1 + **€137,00**

ADD TO CART

|         |
|---------|
| Qty 1-5 |
| €137,00 |

|         |
|---------|
| Qty 6+  |
| €109,50 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



|                                                            |
|------------------------------------------------------------|
| <b>Diameter (mm):</b><br>10.00                             |
| <b>Effective Focal Length EFL (mm):</b><br>30.00           |
| <b>Substrate:</b> <input type="checkbox"/><br><b>N-BK7</b> |

|                                                                        |
|------------------------------------------------------------------------|
| <b>f/#:</b><br>3                                                       |
| <b>Numerical Aperture NA:</b><br>0.17                                  |
| <b>Coating:</b><br>NIR I (600-1050nm)                                  |
| <b>Type:</b><br>Cylinder Lens, Plano-Convex                            |
| <b>Wavelength Range (nm):</b><br>600 - 1050                            |
| <b>Back Focal Length BFL (mm):</b><br>28.67                            |
| <b>Center Thickness CT (mm):</b><br>2.00                               |
| <b>Center Thickness Tolerance (mm):</b><br>±0.1                        |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤0.5% @ 600 - 1050nm |
| <b>Dimensional Tolerance (mm):</b><br>+0.0/-0.2                        |
| <b>Edge Thickness ET (mm):</b><br>1.17                                 |
| <b>Focal Length Tolerance (%):</b><br>±3                               |
| <b>Radius R<sub>1</sub> (mm):</b><br>15.50                             |
| <b>Surface Quality:</b><br>60-40                                       |
| <b>Tilt Tolerance (mm):</b><br>±0.1 over H                             |
| <b>Typical Applications:</b><br>7 J/cm <sup>2</sup> @ 1064nm, 10ns     |
| <b>Wedge Tolerance (arcmin):</b><br>15.00                              |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |