

TECHSPEC® 12mm Dia. x 75mm FL, VIS-NIR Coated, UV Double-Convex Lens



UV Fused Silica Double-Convex (DCX) Lenses



Stock **#63-834** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕

€134,50

ADD TO CART

Qty 1-5

€134,50

Qty 6+

€107,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.00 +0.0/-0.025

Back Focal Length BFL (mm): 74.11
Effective Focal Length EFL (mm): 75.00
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.59 ±0.05
Edge Thickness ET (mm): 2.06
Radius R₁=R₂ (mm): 68.36
Clear Aperture CA (mm): 11.00
f#: 6.25
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.08
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 1000
Damage Threshold, Reference: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant