

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #43-871 ☐ In Stock



1



€24,00

ADD TO CART

Qty 1-5

€24,00

Qty 6+

€18,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Flatness (P-V):  
4 - 6λ

Substrate: ☐  
Float Glass

Surface Quality:  
60-40

Dimensions (mm):

|                                                                                                     |
|-----------------------------------------------------------------------------------------------------|
| 15.0 x 21.0                                                                                         |
| <b>Dimensional Tolerance (mm):</b><br>±0.25                                                         |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≥95% @ 450 - 650nm @ 45°                          |
| <b>Coating:</b><br>Enhanced Aluminum (450-650nm)                                                    |
| <b>Coating Type:</b><br>Metal                                                                       |
| <b>Clear Aperture CA (mm):</b><br>14.00 x 19.95                                                     |
| <b>Edges:</b><br>Seamed, 0.5mm Maximum Edge Chip                                                    |
| <b>Thickness (mm):</b><br>3.00                                                                      |
| <b>Type:</b><br>Flat Mirror                                                                         |
| <b>Wavelength Range (nm):</b><br>450 - 650                                                          |
| <b>Length (mm):</b><br>21.00                                                                        |
| <b>Width (mm):</b><br>15.00                                                                         |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>0.2 J/cm <sup>2</sup> @ 532nm, 10ns |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |