

TECHSPEC® 20.0mm Dia. x 25.0mm FL, Inked, YAG-BBAR Coated Plano-Convex Lens



YAG-BBAR Coated Plano-Convex (PCX) Lenses



Stock **#88-869-INK** [CONTACT US](#)

[Other Coating Options](#)

- 1 + **€56,50**

ADD TO CART

Qty 1-9
€56,50

Qty 10+
€50,75

Volume Pricing
Request Quote

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
20.00 ±0.025

Effective Focal Length EFL (mm): 25.00 @ 587.6nm
Back Focal Length BFL (mm): 22.76
Coating: YAG-BBAR (500-1100nm)
Coating Specification: R _{abs} <0.25% @ 532nm R _{abs} <0.25% @ 1064nm R _{avg} <1.0% @ 500 - 1100nm
Substrate: ☐ N-SF11
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 4.00 ±0.10
Edge Thickness ET (mm): 1.26
Radius R₁ (mm): 19.62
Clear Aperture CA (mm): 19
f/#: 1.25
Numerical Aperture NA: 0.40
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 532 - 1100
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View