

TECHSPEC®

25.4mm Dia. x 25.4mm FL, VIS 0° Coated, Plano-Convex Lens



Stock **#62-569** 3-4 DAYS

[Other Coating Options](#)

-

1

+

€43,50

ADD TO CART

Qty 1-9
€43,50
Qty 10+
€39,25
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40 +0.0/-0.025

Effective Focal Length EFL (mm):

25.40 @ 587.6nm
Back Focal Length BFL (mm): 21.48
Coating: VS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-SF11
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 7.00 ±0.10
Edge Thickness ET (mm): 2.43
Radius R₁ (mm): 19.93
Clear Aperture CA (mm): 24.4
f/#: 1
Numerical Aperture NA: 0.50
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 425 - 675
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View