


## 25mm Dia x 5mm Thickness Uncoated, Potassium Bromide Window



Stock #68-809 3-4 DAYS

⊖ 1 ⊕ **€91,00**

**ADD TO CART**

Qty 1-10

€91,00

Qty 11+

€82,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Abbe Number (v<sub>d</sub>):**  
33.64

**Bevel:**  
Protective as needed

**Diameter (mm):**

25.00 ±0.50

**Thickness (mm):**  
5.00 ±0.50

**Coating:**  
Uncoated

**Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):**  
43

**Density (g/cm<sup>3</sup>):**  
2.753

**Edges:**  
Fine Ground

**Index of Refraction n<sub>d</sub>:**  
1.56

**Knoop Hardness (kg/mm<sup>2</sup>):**  
7

**Poisson's Ratio:**  
0.203

**Solubility, in 100g of H<sub>2</sub>O @ 273K (g):**  
53.48

**Substrate:**  
Potassium Bromide (KBr)

**Surface Quality:**  
60-40

**Type:**  
Protective Window

**Wavelength Range (nm):**  
250 - 26000

**Young's Modulus (GPa):**  
26.8

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Reach 219:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

---