

TECHSPEC® 25mm Dia x -50mm FL, Protected Aluminum, Convex Mirror



Convex Mirrors

Stock #87-657 3-4 DAYS

⊖ 1 ⊕ **€47,50**

ADD TO CART

Qty 1-5

€47,50

Qty 6+

€38,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Focal Length FL (mm):
-50.00

Center Thickness CT (mm):

3.00

Clear Aperture (%):
90.00

Coating:
Protected Aluminum (400-700nm)

Coating Specification:
R_{avg}>85% @ 400 - 700nm

Coating Type:
Metal

Dimensional Tolerance (mm):
+0.0/-0.1

Edge Thickness ET (mm):
2.22

Focal Length Tolerance (%):
±2

Radius R (mm):
100.0

Substrate:
[N-BK7](#)

Surface Accuracy:
λ/2

Surface Quality:
60-40

Thickness Tolerance (mm):
±0.1

Type:
Spherical Mirror

Wavelength Range (nm):
400 - 700

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)
