

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



Stock #89-608 3-4 DAYS

[Other Coating Options](#)



1



€1.075,00

ADD TO CART

Qty 1-5

€1.075,00

Qty 6+

€860,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
15.00 @ 4000nm

Numerical Aperture NA:
0.83

Back Focal Length BFL (mm): 14.00
Substrate: Germanium (Ge)
Aspheric Design Wavelength (nm): 4000
Asphere Figure Error, RMS @ 632.8nm: λ/6
Coating: BBAR (3000-12000nm)
Coating Specification: R _{avg} <5.0% @ 3 - 12μm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 22.5
Edge Thickness ET (mm): 2.47
Center Thickness CT (mm): 4.00 ±0.10
f/#: 0.6
Bevel: Protective bevel as needed
Edges: Diamond Turned
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 3000 - 12000
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant