

## TECHSPEC® 25mm Dia x 25mm FL Acylinder Lens, Uncoated



TECHSPEC Acylinder Lenses

Stock #86-033 3-4 DAYS

⊖ 1 ⊕ **€825,00**

**ADD TO CART**

Qty 1-5

€825,00

Qty 6+

€660,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Diameter (mm):**  
25.00 +0.0/-0.1

**Effective Focal Length EFL (mm):**  
25.00

**Substrate:**   
[NSF5](#)

f#: 1.00

Numerical Aperture NA: 0.50

Coating: Uncoated

Type: Acylinder Lens

Wavelength Range (nm): 380 - 2500

Back Focal Length BFL (mm): 20.2

Center Thickness CT (mm): 8.00

Center Thickness Tolerance (mm):  $\pm 0.1$

Clear Aperture (%): 90.00

Edge Thickness ET (mm): 3.1

Focal Length Specification Wavelength (nm): 587.6

Surface Accuracy, RMS ( $\mu\text{m}$ ): 1.0

Surface Quality: 60-40

## Regulatory Compliance

RoHS 2015: [Compliant](#)

Reach 219: [Compliant](#)

Certificate of Conformance: [View](#)

---