

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #84-128 ☐ In Stock

☐ [Other Coating Options](#)



1



€255,00

ADD TO CART

Qty 1-5

€255,00

Qty 6+

€204,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
2.00 +0.0/-0.025

Effective Focal Length EFL (mm):

4.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 2.92
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 1.6
Centering (arcmin): 30-45
Center Thickness CT (mm): 2.00 ±0.10
Center Thickness CT 1 (mm): 1.00 ±0.05
Center Thickness CT 2 (mm): 1.00 ±0.05
Radius R ₁ (mm): 2.26
Radius R ₂ (mm): -2.26
Radius R ₃ (mm): -10.00
Edge Thickness ET (mm): 1.72
Substrate: ☐ N-PSK53A / N-LASP9
Surface Quality: 20-10
f/#: 2.00
Numerical Aperture NA: 0.25
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @400 - 870nm R _{avg} ≤1.25% @890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View