

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Standard Series

Stock #57-582 3-4 DAYS



1



€86,00

ADD TO CART

Qty 1-4

€86,00

Qty 5+

€76,10

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
1.5, Typical

Maximum Aperture (mm):
25.0

Outer Diameter (mm): 37.0
Construction: Anodized Aluminum Alloy, Burnished Spring Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 13.00
Number of Leaves: 15.00
Thickness (mm): 5.50

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant