

TECHSPEC® 5mm 850nm, Laser Line Polarizing Cube Beamsplitter



TECHSPEC Laser Line Polarizing Cube Beamsplitters

Stock #47-780 3-4 DAYS

⊖ 1 ⊕ **€233,00**

ADD TO CART

Qty 1-5

€233,00

Qty 6+

€182,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Beam Deviation (arcmin):
±3

Bevel:
Protective bevel as needed

Clear Aperture (%):
90.00

Coating Specification:
Rabs <0.25% @ 850nm

Construction:
Cube

Design Wavelength DWL (nm):
850

Dimensions (mm):
5.0 x 5.0 x 5.0 ±0.1

Extinction Ratio:
1000:1

P-Polarization Transmission (%):
>95

S-Polarization Reflection (%):
>99.5

Substrate:
[N-BK7](#)

Surface Quality:
40-20

Type:
Linear Polarizer

Power (fringes) @ 632.8nm:
1.25

Irregularity (fringes) @ 632.8nm:
0.25

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Reach 219:
[Compliant](#)

Certificate of Conformance:
[View](#)
