

TECHSPEC® 6.25mm Dia. x 17.5mm FL, VIS 0° Coated, Achromatic Lens



Stock **#49-937** 3-4 DAYS
[Other Coating Options](#)

⊖ 1 ⊕ **€67,00**

ADD TO CART

Qty 1-5
€67,00
Qty 6+
€53,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.25 +0.0/-0.025

Effective Focal Length EFL (mm):

17.50
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 15.46
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 5.625
Centering (arcmin): <1
Center Thickness CT (mm): 3.75 ±0.10
Center Thickness CT 1 (mm): 2.75 ±0.05
Center Thickness CT 2 (mm): 1.00 ±0.05
Radius R ₁ (mm): 11.13
Radius R ₂ (mm): -9.22
Radius R ₃ (mm): -38.49
Edge Thickness ET (mm): 3.18
Substrate:  N-SSK8 / N-SF56
Surface Quality: 40-20
f/#: 2.8
Numerical Aperture NA: 0.18
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View