

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



UV Fused Silica Double-Convex (DCX) Lenses



Stock **#49-264** 3-4 DAYS

[Other Coating Options](#)



1



€132,50

ADD TO CART

Qty 1-5

€132,50

Qty 6+

€106,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
6.00 +0.0/-0.025

|                                                                                                   |
|---------------------------------------------------------------------------------------------------|
| <b>Back Focal Length BFL (mm):</b><br>11.23                                                       |
| <b>Effective Focal Length EFL (mm):</b><br>12.00                                                  |
| <b>Coating:</b><br>VIS 0° (425-675nm)                                                             |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤0.4% @ 425 - 675nm                             |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">Fused Silica</a> (Corning 7980)         |
| <b>Surface Quality:</b><br>40-20                                                                  |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                                             |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                                                       |
| <b>Centering (arcmin):</b><br><1                                                                  |
| <b>Bevel:</b><br>Protective bevel as needed                                                       |
| <b>Center Thickness CT (mm):</b><br>2.20 ±0.05                                                    |
| <b>Edge Thickness ET (mm):</b><br>1.34                                                            |
| <b>Radius R<sub>1</sub>=R<sub>2</sub> (mm):</b><br>10.65                                          |
| <b>Clear Aperture CA (mm):</b><br>5.4                                                             |
| <b>f/#:</b><br>2.00                                                                               |
| <b>Focal Length Specification Wavelength (nm):</b><br>587.6                                       |
| <b>Focal Length Tolerance (%):</b><br>±1                                                          |
| <b>Numerical Aperture NA:</b><br>0.25                                                             |
| <b>Type:</b><br>Double-Convex Lens                                                                |
| <b>Wavelength Range (nm):</b><br>425 - 675                                                        |
| <b>Damage Threshold, Reference:</b> <input type="checkbox"/><br>5 J/cm <sup>2</sup> @ 532nm, 10ns |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |