

TECHSPEC® 6mm Dia. x 9mm FL, VIS 0° Coated, Double-Convex Lens



Stock **#47-479** ☐ In Stock
[Other Coating Options](#)

1 **€39,50**

ADD TO CART

Qty 1-9
€39,50
Qty 10+
€35,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.00 +0.0/-0.025

Back Focal Length BFL (mm):

8.22
Effective Focal Length EFL (mm): 9.00
Coating: VS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <3
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.25
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.22
Radius R ₁ =R ₂ (mm): 8.91
Clear Aperture CA (mm): 5.4
f/#: 1.5
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.33
Type: Double-Convex Lens
Wavelength Range (nm): 425 - 675
Damage Threshold, Reference: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View