

TECHSPEC® 9mm Dia. x 18mm FL, VIS-NIR Coated, Achromatic Lens



Stock **#49-314** ☐ In Stock
[Other Coating Options](#)

1 **€76,00**

ADD TO CART

Qty 1-5
€76,00
Qty 6+
€60,75
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
9.00 +0.0/-0.025

Effective Focal Length EFL (mm):

18.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 14.91
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 8.1
Centering (arcmin): <1
Center Thickness CT (mm): 5.47 ±0.10
Center Thickness CT 1 (mm): 4.32 ±0.05
Center Thickness CT 2 (mm): 1.15 ±0.05
Radius R ₁ (mm): 12.37
Radius R ₂ (mm): -7.38
Radius R ₃ (mm): -73.86
Edge Thickness ET (mm): 4.49
Substrate:  N-BAF10 / N-SF10
Surface Quality: 40-20
f/#: 2.00
Numerical Aperture NA: 0.25
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @400 - 870nm R _{avg} ≤1.25% @890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View