

Fly's Eye Array 5 x 5mm, 300µm Pitch, 13° Divergence



Microlens Arrays



Stock **#84-132** 3-4 DAYS



1



€245,00

ADD TO CART

Qty 1-10

€245,00

Qty 11+

€214,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
0.60

Substrate: [Fused Silica](#) (Corning 7980)

Coating: Uncoated
Type: Flys Eye Lens Array
Wavelength Range (nm): 200 - 2200
Dimensional Tolerance (mm): ±0.05
Dimensions (mm): 5.0 x 5.0
Divergence Angle (°): ±13
Lens Profile: Spherical
Pitch (µm): 300.00
Pitch Tolerance (µm): ±0.25
Radius R (mm): 0.293
Thickness (mm): 0.90
Thickness Tolerance (mm): ±0.05
Type of Optics: Double-Convex

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View