




NOTES:

- 1. SUBSTRATE
- 2. COATING
S1: Ravg >90% @ 425 - 675nm Tavg >85% @ 800 - 1200nm
- S2: NONE
- 3. FINE GRIND SURFACE
- 4. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS
APPLY ACROSS CLEAR APERTURE
- 5. ROHS COMPLIANT

FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	<div><div><div><div><div></div></div></div><div><div></div></div></div><div>Edmund Optics®</div></div>			
SHAPE	PLANO	PLANO	<div>THIRD ANGLE PROJECTION</div> <div></div>	TITLE	Ø50mm, 0° AOI, Cold Mirror	
SURFACE QUALITY	80-50	80-50				
SURFACE FLATNESS	4 - 6λ	4 - 6λ				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	47305
						SHEET 1 OF 1