NOTES:

1. SUBSTRATE MATERIAL: N-BK7


- 2. ROHS COMPLIANT
- 3. SURFACE S1 TO BE PARALLEL WITH SURFACE S2 TO WITHIN ≤ 3 ARCMIN
- 4. COATING (APPLY ACROSS CLEAR APERTURE)


\$1: 20% R ±5% @ 550nm 80% T ±5% @ 550nm

S2: AR R(avg) ≤1%, R(abs) ≤2% @ 700 - 1100nm

<u>/</u>5.

CUT WITH 0.25mm MAXIMUM EDGE CHIP





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	\$1	\$2
SHAPE	PLANO	PLANO
ANGLE OF INCIDENCE	45°	45°
SURFACE QUALITY 60-40		60-40
SURFACE FLATNESS	1λ PER 25mm	1λ PER 25mm

Edmund Optics®

			-	
THIRD ANGLE PROJECTION	\rightarrow	TITLE	50 x 75mm, 20 R/80 T, PLATE BEAMSPLI	TTER
ALL DIMS IN	mm	DWG NO	68378	SHEET 1 OF 1