



NOTES:

1. SUBSTRATE: GERMANIUM (GE)
2. COATING (APPLY ACROSS COATING APERTURE)

S1: R(avg) <3.0% @ 8 - 12µm

S2: R(avg) <3.0% @ 8 - 12µm


3. EDGES DIAMOND TURNED
4. CENTERING: <3 ARCMIN
5. RoHS COMPLIANT



SECTION F-F

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

SHAPE	CONVEX	S2	EFL @ 10.6µm	100	 <b>Edmund Optics®</b>	TITLE 25mm DIA. X 100mm FL, 8 - 12µm COATED, GE PLANO-CONVEX LEN	DWG NO 69667	SHEET 1 OF 1	
RADIUS	300.39	∞	BFL @ 10.6µm	99.25					
SURFACE QUALITY	60-40	60-40	THIRD ANGLE PROJECTION 						
CLEAR APERTURE	Ø24	Ø24	ALL DIMS IN		mm				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED							