






NOTES:

1. SUBSTRATE: B270
2. RoHS: COMPLIANT
3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN < 4 arcmin
4. S1 & S2:
AR: Ravg <0.5% @ 400 - 700nm



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A					
EXTINCTION RATIO	10000	THIRD ANGLE PROJECTION 	TITLE	12.5mm DIA. HIGH PERFORMANCE LINEAR GLASS POLARIZER	
OPERATING TEMPERATURE (°C)	-25 to +65		DWG NO	47215	SHEET 1 OF 1
SURFACE FLATNESS	<1λ				
TRANSMISSION	25% @ ±2% (for random polarization)		ALL DIMS IN	mm	