



NOTES:

- 1. SUBSTRATE: FUSED SILICA
 - 2. COATING (APPLY ACROSS CLEAR APERTURE)
 - S1: 266nm HR Coating
 - R(ABS) > 99.5% @ 266nm @ 45° AOI
 - R(AVG) > 99.5% FROM 263-268nm @ 45° AOI
- DAMAGE THRESHOLD
PULSED: 2.5 J/cm² , 20ns, 20 Hz @ 266nm
CW: 1MW/cm² @ 266nm

3 FINE GRIND SURFACE

- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	20-10	20-10
CLEAR APERTURE	12.72 x 9.00	Ø9.00
SURFACE FLATNESS	λ/20	λ/20
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION		Edmund Optics®	
ALL DIMS IN		TITLE	10mm, 1/20 WAVE, 266nm, HR CTD HYP, HT RA, FS PRISM
mm		DWG NO	37641
			SHEET 1 OF 1