




NOTES:

1. SUBSTRATE:  
II-VI Infrared ZnSe
2. CENTERING TOLERANCE:  
EDGE THICKNESS VARIATION MEASURED AT THE CLEAR APERTURE OF S1  
NOT TO EXCEED 50.8µm
3. COATING (APPLY ACROSS COATING APERTURE)  
BBAR (8000-12000nm)  
S1 & S2: R(AVG) <0.5% @ 8 - 12µm
4. FINE GROUND SURFACE
5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY  
ACROSS CLEAR APERTURE
6. WAVELENGTH RANGE: 8000 - 12000nm
7. SURFACE ROUGHNESS: <50 Å
8. ROHS: COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2				
SHAPE	CONVEX	PLANO				
RADIUS	17.814	INFINITY	EFL (AT 10.6 microns)	12.70	 <b>Edmund Optics®</b>	
SURFACE QUALITY	40-20	40-20	BFL (AT 10.6 microns)	11.45		
CLEAR APERTURE	90%	90%			TITLE	12.7mm Dia. x 12.7mm FL, 8-12µm BBAR Coated, ZnSe Plano-Convex Lens
POWER at 10.6µm	λ/10	λ/10			DWG NO	39542
IRREGULARITY at 10.6µm	λ/20	λ/20				SHEET 1 OF 1
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm		