

# TECHSPEC® C SERIES

## FIXED FOCAL LENGTH LENSES

### #86-410 • 100mm • f/2.8 - f/22



TECHSPEC® C Series Fixed Focal Length Lenses are designed for use in machine vision applications with the working distance and resolution requirements of factory automation and inspection in mind. TECHSPEC® C Series Fixed Focal Length Lenses feature large maximum apertures, allowing these high performance lenses to be used in even the most restrictive lighting conditions.


<b>Focal Length:</b>	100mm
<b>Working Distance<sup>1</sup>:</b>	750mm - ∞
<b>Max. Sensor Format:</b>	4/3"
<b>Camera Mount:</b>	C-Mount
<b>Aperture (f/#):</b>	f/2.8 - f/22
<b>Distortion %<sup>2</sup>:</b>	<0.05%
<b>Object Space NA<sup>2</sup>:</b>	0.022782

<b>Magnification Range:</b>	0X - 0.160X
<b>Type:</b>	Fixed Focal Length Lens
<b>Length<sup>2</sup>:</b>	92.1mm
<b>Weight:</b>	257g
<b>RoHS:</b>	Compliant
<b>Number of Elements (Groups):</b>	7 (6)
<b>AR Coating:</b>	425 - 675nm BBAR


1. From front housing 2. At Minimum W.D.

At Minimum W.D. (750mm)										
Sensor Size	1/4"	1/3"	1/2.5"	1/2"	1/1.8"	2/3"	1"	1.1"	4/3"	APS-C
<b>Field Of View<sup>3</sup></b>	22.6mm - 2.0°	30.1mm - 2.7°	36.4mm - 3.3°	40.1mm - 3.6°	45.2mm - 4.1°	55.2mm - 5.0°	80.3mm - 7.2°	89.1mm - 8.0°	108.7mm - 9.7°	N/A

3. Horizontal FOV on Standard (4:3) sensor format. Min W.D.




**Figure 1:** Distortion at the maximum sensor format. Positive values correspond to pincushion distortion, negative values correspond to barrel distortion.




**Figure 2:** Relative illumination (center to corner)

In both plots, field points corresponding to the image circle of common sensor formats are included. Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

**MTF & DOF: f/2.8**  
**WD: 750mm**  
**HORIZONTAL FOV: 55mm**



**Figure 3:** Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for  $\lambda = 486\text{nm}$  to  $656\text{nm}$ . Included are the Tangential and Sagittal values for field points on center, at 70% of full field and the maximum sensor format. Solid black line indicates diffraction limit determined by  $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




**Figure 4:** Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.


Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

© COPYRIGHT 2019 EDMUND OPTICS, INC. ALL RIGHTS RESERVED

**MTF & DOF: f/4.0**  
**WD: 750mm**  
**HORIZONTAL FOV: 55mm**



**Figure 5:** Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for  $\lambda = 486\text{nm}$  to  $656\text{nm}$ . Included are the Tangential and Sagittal values for field points on center, at 70% of full field and the maximum sensor format. Solid black line indicates diffraction limit determined by  $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




**Figure 6:** Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.


Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

© COPYRIGHT 2019 EDMUND OPTICS, INC. ALL RIGHTS RESERVED

**MTF & DOF: f/2.8**  
**WD: 1000mm**  
**HORIZONTAL FOV: 77mm**



**Figure 7:** Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for  $\lambda = 486\text{nm}$  to  $656\text{nm}$ . Included are the Tangential and Sagittal values for field points on center, at 70% of full field and the maximum sensor format. Solid black line indicates diffraction limit determined by  $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.



**Figure 8:** Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

MTF & DOF: f/4.0

WD: 1000mm

HORIZONTAL FOV: 77mm




Figure 7: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for  $\lambda = 486\text{nm}$  to  $656\text{nm}$ . Included are the Tangential and Sagittal values for field points on center, at 70% of full field and the maximum sensor format. Solid black line indicates diffraction limit determined by  $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 8: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.