





FOCAL LENGTH (EFL): 150 ±1,5
BACK FOCAL LENGTH (BFL): 142,45

1 AR COATING: NONE

LEFT SURFACE			MATERIAL	RIGHT SURFACE	
R	77,52±0,078 CX		GLASS N-BK7 517/642	R	∞ PL
Øe	73,5			Øe	73,5
3/	3 (0,5) λ=632,8 nm			3/	3 (0,5) λ=632,8 nm
4/	-			4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)			5/	40 - 20 (MIL-PRF-13830B)
6/	-			6/	-
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®	
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	75,0mm Dia, x 150,0mm FL, Uncoated, Plano-Convex Lens
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				ALL DIMS IN:	mm
INDICATIONS IN ACCORDANCE WITH ISO 10110			DWG NO	45369	SHEET SIZE A4
					SHEET 1 OF 1