






FOCAL LENGTH (EFL): 12 ±0,12
 BACK FOCAL LENGTH (BFL): 10,79

1 AR COATING: NIR I
 R(AVG) ≤ 0,5% FROM 600-1050nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	15,34±0,015 CX	GLASS N-SF5 673/322	R	15,34±0,015 CX
Øe	11		Øe	11
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,49'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics®				
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm							
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY					TITLE	12mm Dia, x 12mm FL, NIR I Coated, Double-Convex Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING					DWG NO	49474	SHEET SIZE A4	SHEET 1 OF 1	
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm					