





FOCAL LENGTH (EFL): $18 \pm 0,18$
 BACK FOCAL LENGTH (BFL): $15,61$

1 AR COATING: NONE

LEFT SURFACE			MATERIAL	RIGHT SURFACE	
R	12,11±0,012 CX		GLASS N-SF5 673/322	R	∞ PL
Øe	14			Øe	14
3/	3 (0,5) λ=632,8 nm			3/	3 (0,5) λ=632,8 nm
4/	-			4/	1,49'
5/	40 - 20 (MIL-PRF-13830B)			5/	40 - 20 (MIL-PRF-13830B)
6/	-			6/	-
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®	
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				15,0mm Dia, x 18,0mm FL, Uncoated, Plano-Convex Lens	
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO
					49878
			SHEET SIZE		SHEET
			A4		1 OF 1