




FOCAL LENGTH (EFL): 24 ± 0.24
 BACK FOCAL LENGTH (BFL): 23.31

1 AR COATING: UV-VIS
 R(AVG) ≤ 1.5% FROM 250-700nm @ 0° AOI
 R(ABS) ≤ 1.0% FROM 350-450nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	21,69±0,022 CX	GLASS FUSED SILICA 458/678	R	21,69±0,022 CX
Øe	5,4		Øe	5,4
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			TITLE	6mm Dia, x 24mm, UV-VIS Coated, UV Double-Convex Lens	
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			ALL DIMS IN: mm				
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				DWG NO	49992		SHEET SIZE A4
INDICATIONS IN ACCORDANCE WITH ISO 10110							